

General Information

Extended Product Type:	M4/6
Product ID:	1SNA105031R1400
EAN:	3472591050318
Catalog Description:	M4/6 Screw Clamp Terminal Blocks - Feed-through - Black
Long Description:	- Flexibility: snap onto symmetrical and asymmetrical rails, - Many colors are available in addition to our generic grey to help you quickly identify any specific functions.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
CSA Certificate:	1SND161039A0201
Color:	Black
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 22 ... 10 AWG Screw Clamp / Rigid 1x 22 ... 10 AWG Screw Clamp / Rigid 2x 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ² Screw Clamp / With Insulated Ferrule 1x 2.5 mm ²
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225014U1000
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	2000 V
EAC Certificate:	1SND161009A1100
EAN:	3472591050318
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220001E1002
Flammability According to UL94:	V0
Function:	Feed-through
Gauge Type:	A4
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Insulation Material:	Polyamide
Invoice Description:	M4/6 Screw Clamp Terminal Blocks - Feed-through - Black
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472591050318
Package Level 1 Gross Weight:	0.41 kg
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 2 Gross Weight:	18.100 kg
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	2000 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	48000 piece
Pollution Degree:	3
Power Loss:	1 W
Product Main Type:	M4/6
Product Name:	Terminal block
Product Net Depth:	40.5 mm
Product Net Height:	44.5 mm
Product Net Length:	40.5 mm
Product Net Weight:	8.2 g
Product Net Width:	6 mm
Product Packing Type:	Box
RMRS Certificate:	1SND161007A1101
Rated Cross-Section:	4 mm ²
Rated Current (I _n):	Main Circuit 32 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Rated Short-time Withstand Current (I _{cw}):	for 1 s 480 A
Rated Voltage (U _r):	1000 V
Recommended Screw Driver:	4 mm
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	black Screw Clamp Terminal Blocks M4/6
Spacing:	6 mm
Sub-Function:	2 connections
Sub-Function 3:	2 connections
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
Wire Stripping Length:	9.5 mm
cUL Certificate:	1SND161001A0209

