


KEMET Part Number: ALS30A153DB040
(A331FD153M040A)

ALS30, Aluminum Electrolytic, 15,000 uF, 20%, 40 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	ALS30
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M8x12. Mounting Clip (Sold Separately): V3/H2/UTE2736
Shelf Life:	156 Weeks

Dimensions

D	36mm +/-1mm
L	62mm +/-2mm
T	7.14mm +/-0.5mm
S	12.8mm +/-0.5mm
DT	8mm +/-0.5mm
LT	67.5mm +/-1mm
TD	10mm MIN
V	8mm NOM

Specifications

Capacitance:	15,000 uF
Capacitance Tolerance:	20%
Voltage DC:	40 VDC, 46 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	11000 Hrs (Rated Voltage And Ripple Current At 85C), 22000 Hrs (Rated Voltage At 85C)
Resistance:	17 mOhms (100Hz 20C), 14 mOhms (10kHz 20C)
Ripple Current:	9.5 Amps (100Hz 85C), 10 Amps (10kHz 85C)
Leakage Current:	3600 uA (5min 20°C)

Packaging Specifications

Weight:	90 g
Sleeving:	Yes
Packaging:	Bulk, Box

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.