



Inductive sensor with extended switching distance Bi2-EG08-VP6X-H1341



- threaded barrel, M8 x 1
- stainless steel, 1.4404
- large detection range
- 4-wire DC, 10...30 VDC
- change-over, pnp output
- connector, M12 x 1

Wiring diagram



Functional principle

Inductive sensors are designed for wear-free and non-contact detection of metal objects. For this purpose they use a high-frequency electro-magnetic AC field that interacts with the target. With inductive sensors, this field is generated by an LC resonant circuit with a ferrite core coil.

Type	Bi2-EG08-VP6X-H1341
Ident-No.	4602522
Rated operating distance Sn	2 mm
Mounting condition	flush
Assured sensing range	$\leq (0,81 \times S_n) \text{ mm}$
Correction factors	$S_{37} = 1, V_{2A} \sim 0.7, M_s \sim 0.4, A_I \sim 0.3$
Repeatability	$\leq 2 \%$
Temperature drift	$\leq \pm 10 \%$
Hysteresis	3... 15 %
Ambient temperature	-25... + 70 °C
Operating voltage	10... 30VDC
Residual ripple	$\leq 10 \% U_{ss}$
DC rated operational current	$\leq 150 \text{ mA}$
No-load current I_0	$\leq 15 \text{ mA}$
Residual current	$\leq 0.1 \text{ mA}$
Rated insulation voltage	$\leq 0.5 \text{ kV}$
Short-circuit protection	yes / cyclic
Voltage drop at I_e	$\leq 1.8 \text{ V}$
Wire breakage / Reverse polarity protection	yes / complete
Output function	4-wire, change-over, pnp
Switching frequency	$\leq 2 \text{ kHz}$
Housing	threaded barrel, M8 x 1
Dimensions	57 mm
Housing material	metal, AISI 316L
Material active face	plastic, plastic, PA12-GF20
Tightening torque of housing nut	10 Nm
Connection	connectors, M12 x 1
Vibration resistance	55 Hz (1 mm)
Shock resistance	30g (11 ms)
Degree of protection	IP67
Display switch state	LED yellow


Inductive sensor with extended switching distance Bi2-EG08-VP6X-H1341

Mounting instructions



	minimum distances
Distance D	$2 \times B$
Distance W	$3 \times S_n$
Distance T	$3 \times B$
Distance S	$1,5 \times B$
Distance G	$6 \times S_n$

Diameter of the active area B

Ø 8 mm



Accessories

Type code	Ident-No.	Short text	Dimension drawing
QM-08	6945100	quick-mount fixing clamp with dead-stop; material: chrome-plated brass male thread M12 x 1. Note: The switching distance of proximity switches can be reduced by the use of quick mounting brackets.	
BST-08B	6947210	fixing clamp with dead-stop; material: PA6	
MW-08	6945008	mounting bracket; material: stainless steel A2 1.4301 (AISI 304)	
BSS-08	6901322	fixing clamp; material: polypropylene	