

Touch panel - WP 07T/WS - 2700307

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Touch panel with 17.8 cm (7") graphics-capable TFT widescreen display, 800 x 480 pixels, 1 x Ethernet, 2 x USB, and integrated micro browser

Why buy this product

- Short startup time
- Easy installation, low installation depth, and compact design
- Low maintenance costs - projects are only adapted once
- Micro browser (WebVisit client) integrated as standard in all devices
- Display available in sizes from 8.9 cm (3.5") to 38.1 cm (15")
- Easy device replacement - the visualization project is saved on the PLC (web server)

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 547949
Weight per Piece (excluding packing)	4440.0 g
Custom tariff number	85371099
Country of origin	Germany

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

External dimension, width	203 mm
External dimension, height	147 mm
External dimension, depth	5 mm
Note regarding external dimension	Dimensions of the front plate
Installation dimension, width	195 mm
Installation dimension, height	139 mm
Note regarding installation dimension	Installation cutout

Display

Touch panel - WP 07T/WS - 2700307

Technical data

Display

Display	17.8 cm/7" TFT
Resolution	800 x 480 Pixel (WVGA)
Backlighting	LED
Display backlight MTBF	> 50000 h
Touch screen	Resistive industrial touch screen
Colors	65,536 colors

Computer data

Processor	RISC ARM9™ CPU; 200 MHz
RAM	64 MByte SDRAM
Mass storage	32 MByte flash memory
Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Operating systems	Windows CE 5.0

General

Mounting type	Installation in front plate
Weight	1000 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Classifications

eCl@ss

eCl@ss 4.0	27330201
eCl@ss 4.1	27330201
eCl@ss 5.0	27330201
eCl@ss 5.1	27242301
eCl@ss 6.0	27242301
eCl@ss 7.0	27242301
eCl@ss 8.0	27242301

ETIM

ETIM 3.0	EC001414
ETIM 4.0	EC001414

Touch panel - WP 07T/WS - 2700307

Classifications

ETIM

ETIM 5.0	EC001414
----------	----------

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43211507
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

GL / GL-SW / UL Listed / cUL Listed / UL Listed / cUL Listed / GL / GL-SW / GL / cULus Listed

Ex Approvals

Approvals submitted

Approval details

GL

GL-SW

UL Listed

cUL Listed

UL Listed

Touch panel - WP 07T/WS - 2700307

Approvals

cUL Listed 

GL

GL-SW

GL

cULus Listed 

Accessories

Accessories

Mounting material

Mounting kit - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



Mounting material - HMI WALL BOX - 2701381



Flush-type box made of galvanized sheet steel for panel mounting.

Mounting kit - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Touch panel - WP 07T/WS - 2700307

Accessories

Mounting kit - HMI SCB MOUNTING KIT 6 - 2701385



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

Mounting kit - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for HMIs, silver coated. Delivery includes self-adhesive pen holder.

Protective foil

Protective foil - 7" DISPLAY PROTECTIVE FOIL - 2701374



Protective film set comprising 10 pieces of film for a 7" display. Including a squeegee to apply film and instructions.

Storage medium

USB memory stick - 2 GB USB STICK - 2701382



USB memory stick, 2 GB.
