

8461 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacket Con



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG stranded (7x26) tinned copper conductors, PVC insulation, twisted pair, PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	18	7x26	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.5588

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.686

Overall Cable

Overall Nominal Diameter: 5.944 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & White

Pair Lay Length & Direction:

Lay Length (mm)	Twists (twist/m)	Direction
50.800	19.686	Left Hand

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

Bulk Cable Weight: 35.717 Kg/Km

Max. Recommended Pulling Tension: 200.169 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC(UL) Specification: CL3, CMG

NEC Articles: 800, 725

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (RoHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

METRIC MEASUREMENT VERSION

8461 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacket Con

CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4
Suitability	
Suitability - Indoor:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
72.182

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
19.2267

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Description	Current
10C Temperature Rise	4.8 Amps per conductor @ 20°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8461 060U1000	1,000 FT	26.000 LB	CHROME		2 #18 PVC FRPVC
8461 060U500	500 FT	14.000 LB	CHROME		2 #18 PVC FRPVC
8461 060100	100 FT	3.200 LB	CHROME		2 #18 PVC FRPVC
8461 0601000	1,000 FT	27.000 LB	CHROME	C	2 #18 PVC FRPVC
8461 060500	500 FT	13.500 LB	CHROME	C	2 #18 PVC FRPVC
8461 0605000	5,000 FT	140.000 LB	CHROME		2 #18 PVC FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 08-05-2013

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.