



SAFETY DATA SHEET

Cardclene Plain Cards 20 Sachets

According to Regulation (EC) No 1907/2006, Annex II, as amended.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Cardclene Plain Cards 20 Sachets

Product number ACCP020, ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier AF INTERNATIONAL. A division of HK WENTWORTH LTD
 ASHBY PARK
 COALFIELD WAY
 ASHBY de la ZOUCH
 LEICESTERSHIRE. LE65 1JR
 UNITED KINGDOM
 +44 (0) 1530 419600
 +44 (0) 1530 416640
 info@hkw.co.uk

1.4. Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:
 +44 1865 407333 (24hr, Provided by Carechem 24)
 +353 (0)1 809 2166 (Beaumont Hospital, Republic of Ireland only, 8am-10pm, 7 days a week)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)


Physical hazards Flam. Liq. 2 - H225

Health hazards Eye Irrit. 2 - H319 STOT SE 3 - H336

Environmental hazards Not Classified

2.2. Label elements

Pictogram



Signal word Danger

Hazard statements H225 Highly flammable liquid and vapour.
 H319 Causes serious eye irritation.
 H336 May cause drowsiness or dizziness.

Cardclene Plain Cards 20 Sachets

Precautionary statements	<p>P102 Keep out of reach of children.</p> <p>P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.</p> <p>P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower.</p> <p>P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>
Contains	Propan-2-ol
Supplementary precautionary statements	<p>P240 Ground and bond container and receiving equipment.</p> <p>P241 Use explosion-proof electrical equipment.</p> <p>P242 Use non-sparking tools.</p> <p>P243 Take action to prevent static discharges.</p> <p>P261 Avoid breathing vapour/ spray.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.</p> <p>P312 Call a POISON CENTRE/doctor if you feel unwell.</p> <p>P337+P313 If eye irritation persists: Get medical advice/ attention.</p> <p>P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish.</p> <p>P403+P233 Store in a well-ventilated place. Keep container tightly closed.</p> <p>P403+P235 Store in a well-ventilated place. Keep cool.</p>

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Propan-2-ol			60-100%
CAS number: 67-63-0	EC number: 200-661-7	REACH registration number: 01-2119457558-25-XXXX	
Classification			
Flam. Liq. 2 - H225			
Eye Irrit. 2 - H319			
STOT SE 3 - H336			

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention. Place unconscious person on their side in the recovery position and ensure breathing can take place.

Cardclene Plain Cards 20 Sachets

Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Never give anything by mouth to an unconscious person. Place unconscious person on their side in the recovery position and ensure breathing can take place. Keep affected person under observation. Get medical attention.
Skin contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Keep upwind to avoid inhalation of gases, vapours, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

Cardclene Plain Cards 20 Sachets

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid inhalation of dust and vapours. Use suitable respiratory protection if ventilation is inadequate.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store locked up. Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class Flammable solid storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

Propan-2-ol

Cardclene Plain Cards 20 Sachets

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m³

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

No specific hand protection recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.

Respiratory protection

No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	12°C Closed cup.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.

Cardclene Plain Cards 20 Sachets

Relative density	0.7855 @ 20°C
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions The following materials may react strongly with the product: Oxidising agents.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.

10.5. Incompatible materials

Materials to avoid Oxidising materials. Acids - oxidising.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Cardclene Plain Cards 20 Sachets

Serious eye damage/irritation	Causes serious eye irritation.
<u>Respiratory sensitisation</u>	
Respiratory sensitisation	Based on available data the classification criteria are not met.
<u>Skin sensitisation</u>	
Skin sensitisation	Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
Carcinogenicity	Based on available data the classification criteria are not met.
IARC carcinogenicity	Contains a substance which may be potentially carcinogenic. IARC Group 3 Not classifiable as to its carcinogenicity to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	STOT SE 3 - H336 May cause drowsiness or dizziness.
Target organs	Central nervous system
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Aspiration hazard	Based on available data the classification criteria are not met.
General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target organs	Central nervous system
<u>Toxicological information on ingredients.</u>	

Propan-2-ol

Acute toxicity - dermal

Notes (dermal LD₅₀)

LD₅₀ 5840 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

Skin corrosion/irritation

Cardclene Plain Cards 20 Sachets

Animal data	Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.
<u>Serious eye damage/irritation</u>	
Serious eye damage/irritation	Dose: 0.1 mL, 1 second, Rabbit Causes serious eye irritation.
<u>Skin sensitisation</u>	
Skin sensitisation	Buehler test - Guinea pig: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.
Genotoxicity - in vivo	Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
Carcinogenicity	NOAEL 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.
IARC carcinogenicity	IARC Group 3 Not classifiable as to its carcinogenicity to humans.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	STOT SE 3 - H336 May cause drowsiness or dizziness.
Target organs	Central nervous system
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	NOAEC 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

12.1. Toxicity

Toxicity Based on available data the classification criteria are not met.

Ecological information on ingredients.

Propan-2-ol

Toxicity	Aquatic toxicity is unlikely to occur. Based on available data the classification criteria are not met.
<u>Acute aquatic toxicity</u>	
Acute toxicity - fish	LC ₅₀ , 96 hours: 10000 mg/l, Pimephales promelas (Fat-head Minnow)
Acute toxicity - aquatic invertebrates	LC ₅₀ , 24 hours: >10000 mg/l, Daphnia magna
Acute toxicity - aquatic plants	EC ₅₀ , 7 days: 1800 mg/l, Scenedesmus quadricauda

12.2. Persistence and degradability

Cardclene Plain Cards 20 Sachets

Persistence and degradability The degradability of the product is not known.

Ecological information on ingredients.

Propan-2-ol

Persistence and degradability	The substance is readily biodegradable.
Biodegradation	Water - Degradation 53%: 5 days
Biological oxygen demand	1.19-1.72 g O ₂ /g substance
Chemical oxygen demand	2.23 g O ₂ /g substance

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
Partition coefficient	Not available.

Ecological information on ingredients.

Propan-2-ol

Bioaccumulative potential	Bioaccumulation is unlikely.
----------------------------------	------------------------------

12.4. Mobility in soil

Mobility	No data available.
-----------------	--------------------

Ecological information on ingredients.

Propan-2-ol

Mobility	The product is soluble in water.
-----------------	----------------------------------

12.5. Results of PBT and vPvB assessment

Ecological information on ingredients.

Propan-2-ol

Results of PBT and vPvB assessment	This substance is not classified as PBT or vPvB according to current EU criteria.
---	---

12.6. Other adverse effects

Other adverse effects	None known.
------------------------------	-------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

Cardclene Plain Cards 20 Sachets

General For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.

14.1. UN number

UN No. (ADR/RID)	3175
UN No. (IMDG)	3175
UN No. (ICAO)	3175
UN No. (ADN)	3175

14.2. UN proper shipping name

Proper shipping name (ADR/RID)	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (CONTAINS PROPAN-2-OL)
Proper shipping name (IMDG)	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (CONTAINS PROPAN-2-OL)
Proper shipping name (ICAO)	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (CONTAINS PROPAN-2-OL)
Proper shipping name (ADN)	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (CONTAINS PROPAN-2-OL)

14.3. Transport hazard class(es)

ADR/RID class	4.1
ADR/RID classification code	F1
ADR/RID label	4.1
IMDG class	4.1
ICAO class/division	4.1
ADN class	4.1

Transport labels



14.4. Packing group

ADR/RID packing group	II
IMDG packing group	II
ICAO packing group	II
ADN packing group	II

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant
No.

14.6. Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS	F-A, S-I
ADR transport category	2
Emergency Action Code	1Z

Cardclene Plain Cards 20 Sachets

Hazard Identification Number 40
(ADR/RID)

Tunnel restriction code (E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	Health and Safety at Work etc. Act 1974 (as amended). The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
EU legislation	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 453/2010 of 20 May 2010. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Dangerous Preparations Directive 1999/45/EC. Dangerous Substances Directive 67/548/EEC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Classification procedures according to Regulation (EC) 1272/2008	STOT SE 3 - H336: Eye Irrit. 2 - H319: : Calculation method. Flam. Liq. 2 - H225: : Expert judgement.
Training advice	Read and follow manufacturer's recommendations.
Issued by	Bethan Massey
Revision date	24/05/2016
Revision	1
SDS number	233
Hazard statements in full	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.