

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




LSA-PLUS plug (COMTRAB CT 10) with surge voltage coarse and fine protection and decoupling resistance for 10 floating signal circuits. Nominal voltage: 24 V DC/AC. Design: 10 double wires

Why buy this product

- ✓ For use with CT-TERMIBLOCK and with LSA-PLUS and LSA-PROFIL disconnect and control strips
- ✓ Multi-position, plug-in modular design
- ✓ Applications include systems with higher signal voltages
- ✓ Combined protective circuits
- ✓ Protection modules must be inserted in the correct direction



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 104757
Weight per Piece (excluding packing)	119.0 g
Custom tariff number	85363010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	22 mm
Width	111 mm
Depth	68.5 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 75 °C
Degree of protection	IP20

General

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Technical data

General

Housing material	PBT
Inflammability class according to UL 94	V0
Color	black
Standards for air and creepage distances	VDE 0110-1
	IEC 60664-1
Mounting type	On CT-TERMIBLOCK and LSA-PLUS disconnect strip
Type	LSA-PLUS module
Direction of action	Line-Line & Line-Earth Ground
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00

Protective circuit

IEC test classification	C1
	C2
	C3
	D1
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	40 V DC
	28 V AC
Maximum continuous voltage U_C (wire-wire)	40 V DC
	28 V AC
Nominal current I_N	200 mA (25 °C)
Operating effective current I_C at U_C	$\leq 5 \mu\text{A}$ (a-b)
Residual current I_{PE}	$\leq 1 \mu\text{A}$ (per path)
Nominal discharge current I_n (8/20) μs (Core-Core)	5 kA
Nominal discharge current I_n (8/20) μs (Core-Earth)	5 kA
Total surge current (8/20) μs	10 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Core)	5 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Earth)	5 kA
Output voltage limitation at 1 kV/ μs (Core-Core) spike	$\leq 95 \text{ V}$
Output voltage limitation at 1 kV/ μs (Core-Earth) spike	$\leq 650 \text{ V}$
Output voltage limitation at 1 kV/ μs (Core-Core) static	$\leq 60 \text{ V}$
Output voltage limitation at 1 kV/ μs (Core-Earth) static	$\leq 650 \text{ V}$
Residual voltage at I_n , (conductor-conductor)	$\leq 55 \text{ V}$
Response time t_A (Core-Core)	$\leq 1 \text{ ns}$
Response time t_A (Core-Earth)	$\leq 100 \text{ ns}$
Input attenuation a_E , sym.	1.5 dB (Typ. up to 2 MHz / 50 Ω)
	0.6 dB (Typ. up to 1 MHz / 150 Ω)
	0.2 dB (Typ. up to 100 kHz / 600 Ω)
Cut-off frequency f_g (3 dB), sym. in 50 Ohm system	7 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 150 Ohm system	4 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 600 Ohm system	900 kHz (typ.)

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Technical data

Protective circuit

Capacity (Core-Core)	1.1 nF (f=1 MHz / V _R = 0 V)
Capacity (Core-Earth)	1 pF (typ.)
Resistance in series	10 Ω ±10 %
	10 Ω ±10 %
Surge protection fault message	None
Max. required back-up fuse	200 mA
Impulse durability (conductor-conductor)	C1 - 1 kV/500 A
	C2 - 10 kV/5 kA
	C3 - 100 A
Impulse durability (conductor-ground)	C1 - 1 kV/500 A
	C2 - 10 kV/5 kA
	C3 - 100 A
	D1 - 2,5 kA

Connection data

Connection method	can be plugged into COMTRAB-TERMIBLOCK and LSA-PLUS disconnect and switching strips
Connection type IN	COMTRAB plug-in system
Connection type OUT	COMTRAB plug-in system

Standards and Regulations

Standards/regulations	IEC 61643-21
-----------------------	--------------

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
-------------	----------

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Classifications

UNSPSC

UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Screw termination block

Screw termination block - CT-TERMIBLOCK 10 DA - 0441711



Screw termination block with disconnect contacts for accommodating protective plugs CT and CTM. Use in MCR and telecommunications systems. Design: 10 double wires

Necessary add-on products

Disconnect strip - CT 10-TL - 2765356



LSA-PLUS disconnect strip to hold the CTM and CT 10 protection modules. Version: 10 double conductors, dimension A: 124 mm.

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Accessories

Additional products

Mounting clip - CT 10-MB/ 3 - 2765372



Mounting clip, for holding 3 disconnect or ground wire strips. Version: 10 double conductors, dimensions: A 104.5 mm, B 65 mm.

Mounting clip - CT 10-MB/10 - 2765385



Mounting clip, for holding 10 disconnect or ground wire strips. Version: 10 double conductors, dimensions: A 104.5 mm, dimensions B 245.5 mm

Cable feed-through sleeve - CT-KDT - 2765518



Cable bush for assembly troughs, for protection of the lines guided through the laminated frame

Shield connection - SSA 3-6 - 2839295



shield fast connections for conductor diameter 3 - 6 mm. Potential connection cable: 200 mm, black

Shield connection - SSA 5-10 - 2839512




Shield fast connection for conductor diameters 5 - 10 mm. Potential connection cable: 200 mm, black

Drawings

Surge protection plug - CT 10-2PE/FSR-24 - 2807968

Circuit diagram



Dimensioned drawing

