



## MPSA06




TO-92

## MMBTA06



SOT-23  
Mark: 1G

## PZTA06



SOT-223

## NPN General Purpose Amplifier

This device is designed for general purpose amplifier applications at collector currents to 300 mA. Sourced from Process 33.

### Absolute Maximum Ratings\*

TA = 25°C unless otherwise noted

| Symbol         | Parameter                                        | Value       | Units |
|----------------|--------------------------------------------------|-------------|-------|
| $V_{CEO}$      | Collector-Emitter Voltage                        | 80          | V     |
| $V_{CBO}$      | Collector-Base Voltage                           | 80          | V     |
| $V_{EBO}$      | Emitter-Base Voltage                             | 4.0         | V     |
| $I_C$          | Collector Current - Continuous                   | 500         | mA    |
| $T_J, T_{stg}$ | Operating and Storage Junction Temperature Range | -55 to +150 | °C    |

\*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

#### NOTES:

- 1) These ratings are based on a maximum junction temperature of 150 degrees C.
- 2) These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

### Thermal Characteristics

TA = 25°C unless otherwise noted

| Symbol          | Characteristic                                | Max        |            |              | Units       |
|-----------------|-----------------------------------------------|------------|------------|--------------|-------------|
|                 |                                               | MPSA06     | *MMBTA06   | **PZTA06     |             |
| $P_D$           | Total Device Dissipation<br>Derate above 25°C | 625<br>5.0 | 350<br>2.8 | 1,000<br>8.0 | mW<br>mW/°C |
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case          | 83.3       |            |              | °C/W        |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient       | 200        | 357        | 125          | °C/W        |

\*Device mounted on FR-4 PCB 1.6" X 1.6" X 0.06."

\*\*Device mounted on FR-4 PCB 36 mm X 18 mm X 1.5 mm; mounting pad for the collector lead min. 6 cm<sup>2</sup>.

NPN General Purpose Amplifier  
(continued)

Electrical Characteristics TA = 25°C unless otherwise noted



| Symbol                       | Parameter                             | Test Conditions                                                                             | Min        | Max  | Units         |
|------------------------------|---------------------------------------|---------------------------------------------------------------------------------------------|------------|------|---------------|
| OFF CHARACTERISTICS          |                                       |                                                                                             |            |      |               |
| $V_{(BR)CEO}$                | Collector-Emitter Sustaining Voltage* | $I_C = 1.0\text{ mA}, I_B = 0$                                                              | 80         |      | V             |
| $V_{(BR)EBO}$                | Emitter-Base Breakdown Voltage        | $I_E = 100\text{ }\mu\text{A}, I_C = 0$                                                     | 4.0        |      | V             |
| $I_{CEO}$                    | Collector-Cutoff Current              | $V_{CE} = 60\text{ V}, I_B = 0$                                                             |            | 0.1  | $\mu\text{A}$ |
| $I_{CBO}$                    | Collector-Cutoff Current              | $V_{CB} = 80\text{ V}, I_E = 0$                                                             |            | 0.1  | $\mu\text{A}$ |
| ON CHARACTERISTICS           |                                       |                                                                                             |            |      |               |
| $h_{FE}$                     | DC Current Gain                       | $I_C = 10\text{ mA}, V_{CE} = 1.0\text{ V}$<br>$I_C = 100\text{ mA}, V_{CE} = 1.0\text{ V}$ | 100<br>100 |      |               |
| $V_{CE(sat)}$                | Collector-Emitter Saturation Voltage  | $I_C = 100\text{ mA}, I_B = 10\text{ mA}$                                                   |            | 0.25 | V             |
| $V_{BE(on)}$                 | Base-Emitter On Voltage               | $I_C = 100\text{ mA}, V_{CE} = 1.0\text{ V}$                                                |            | 1.2  | V             |
| SMALL SIGNAL CHARACTERISTICS |                                       |                                                                                             |            |      |               |
| $f_T$                        | Current Gain - Bandwidth Product      | $I_C = 10\text{ mA}, V_{CE} = 2.0\text{ V},$<br>$f = 100\text{ MHz}$                        | 100        |      | MHz           |

\*Pulse Test: Pulse Width  $\leq 300\text{ }\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$

Spice Model

NPN (Is=8.324f Xti=3 Eg=1.11 Vaf=100 Bf=12.16K Ne=1.368 Ise=73.27f Ikf=.1096 Xtb=1.5 Br=11.1 Nc=2 Isc=0 Ikr=0 Rc=.25 Cjc=18.36p Mjc=.3843 Vjc=.75 Fc=.5 Cje=55.61p Mje=.3834 Vje=.75 Tr=72.15n Tf=516.1p Itf=.5 Vtf=4 Xtf=6 Rb=10)







Typical Characteristics



# NPN General Purpose Amplifier (continued)



MPSA06 / MMbTA06 / PZTA06

## Typical Characteristics (continued)



NPN General Purpose Amplifier  
(continued)

Typical Characteristics (continued)



MPSA06 / MMbTA06 / PZTA06

# TO-92 Tape and Reel Data



## TO-92 Packaging Configuration: Figure 1.0


FSCINT Label sample



F63TNR Label sample



### TAPE and REEL OPTION See Fig 2.0 for various Reeling Styles




### TO-92 TNR/AMMO PACKING INFORMATION

| Packing | Style | Quantity | EOL code |
|---------|-------|----------|----------|
| Reel    | A     | 2,000    | D26Z     |
|         | E     | 2,000    | D27Z     |
| Ammo    | M     | 2,000    | D74Z     |
|         | P     | 2,000    | D75Z     |

Unit weight = 0.22 gm  
 Reel weight with components = 1.04 kg  
 Ammo weight with components = 1.02 kg  
 Max quantity per intermediate box = 10,000 units


### AMMO PACK OPTION See Fig 3.0 for 2 Ammo Pack Options



### (TO-92) BULK PACKING INFORMATION



| EOL CODE    | DESCRIPTION                                                                           | LEADCLIP DIMENSION | QUANTITY    |
|-------------|---------------------------------------------------------------------------------------|--------------------|-------------|
| J18Z        | TO-18 OPTION STD                                                                      | NO LEAD CLIP       | 2.0 K / BOX |
| J05Z        | TO-5 OPTION STD                                                                       | NO LEAD CLIP       | 1.5 K / BOX |
| NO EOL CODE | TO-92 STANDARD STRAIGHT FOR: PKG 92, 94 (NON PROELECTRON SERIES), 96                  | NO LEADCLIP        | 2.0 K / BOX |
| L34Z        | TO-92 STANDARD STRAIGHT FOR: PKG 94 (PROELECTRON SERIES BCXXX, BFXXX, BSRXXX), 97, 98 | NO LEADCLIP        | 2.0 K / BOX |

### BULK OPTION See Bulk Packing Information table





# TO-92 Tape and Reel Data, continued

## TO-92 Reeling Style Configuration: Figure 2.0




## TO-92 Radial Ammo Packaging Configuration: Figure 3.0



# TO-92 Tape and Reel Data, continued


## TO-92 Tape and Reel Taping Dimension Configuration: Figure 4.0



| ITEM DESCRIPTION                   | SYMBOL | DIMENSION              |
|------------------------------------|--------|------------------------|
| Base of Package to Lead Bend       | b      | 0.098 (max)            |
| Component Height                   | Ha     | 0.928 (+/- 0.025)      |
| Lead Clinch Height                 | HO     | 0.630 (+/- 0.020)      |
| Component Base Height              | H1     | 0.748 (+/- 0.020)      |
| Component Alignment ( side/side )  | Pd     | 0.040 (max)            |
| Component Alignment ( front/back ) | Hd     | 0.031 (max)            |
| Component Pitch                    | P      | 0.500 (+/- 0.020)      |
| Feed Hole Pitch                    | PO     | 0.500 (+/- 0.008)      |
| Hole Center to First Lead          | P1     | 0.150 (+0.009, -0.010) |
| Hole Center to Component Center    | P2     | 0.247 (+/- 0.007)      |
| Lead Spread                        | F1/F2  | 0.104 (+/- 0.010)      |
| Lead Thickness                     | d      | 0.018 (+0.002, -0.003) |
| Cut Lead Length                    | L      | 0.429 (max)            |
| Taped Lead Length                  | L1     | 0.209 (+0.051, -0.052) |
| Taped Lead Thickness               | t      | 0.032 (+/- 0.006)      |
| Carrier Tape Thickness             | t1     | 0.021 (+/- 0.006)      |
| Carrier Tape Width                 | W      | 0.708 (+0.020, -0.019) |
| Hold - down Tape Width             | WO     | 0.236 (+/- 0.012)      |
| Hold - down Tape position          | W1     | 0.035 (max)            |
| Feed Hole Position                 | W2     | 0.360 (+/- 0.025)      |
| Sprocket Hole Diameter             | DO     | 0.157 (+0.008, -0.007) |
| Lead Spring Out                    | S      | 0.004 (max)            |

Note : All dimensions are in inches.

## TO-92 Reel Configuration: Figure 5.0





| ITEM DESCRIPTION                 | SYMBOL | MINIMUM | MAXIMUM |
|----------------------------------|--------|---------|---------|
| Reel Diameter                    | D1     | 13.975  | 14.025  |
| Arbor Hole Diameter (Standard)   | D2     | 1.160   | 1.200   |
| Arbor Hole Diameter (Small Hole) | D3     | 0.650   | 0.700   |
| Core Diameter                    | D4     | 3.100   | 3.300   |
| Hub Recess Inner Diameter        | D5     | 2.700   | 3.100   |
| Hub Recess Depth                 | D6     | 0.370   | 0.570   |
| Flange to Flange Inner Width     | W1     | 1.630   | 1.690   |
| Hub to Hub Center Width          | W2     |         | 2.090   |
| Hub to Hub Center Width          | W3     |         |         |

Note: All dimensions are inches

## TO-92 Package Dimensions



### TO-92 (FS PKG Code 92, 94, 96)




Scale 1:1 on letter size paper

Dimensions shown below are in:  
inches [millimeters]

Part Weight per unit (gram): 0.1977

TO-92 (92,94,96)

| PIN | 92 |   | 94 |   | 96 |   |
|-----|----|---|----|---|----|---|
|     | B  | F | B  | F | B  | F |
| 1   | E  | D | E  | D | B  | S |
| 2   | B  | S | C  | G | E  | D |
| 3   | C  | G | B  | S | C  | G |






## SOT-23 Tape and Reel Data



**SOT-23 Packaging Configuration:** Figure 10



### Packaging Description:

SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 177mm diameter reel. The reels are dark blue in color and are made of polystyrene plastic (anti-static coated). Other option comes in 10,000 units per 13" or 330mm diameter reel. This and some other options are described in the Packaging Information table.

These full reels are individually labeled and placed inside a standard intermediate made of recyclable corrugated brown paper with a Fairchild logo printing. One pizza box contains eight reels maximum. And these intermediate boxes are placed inside a labeled shipping box which comes in different sizes depending on the number of parts shipped.

| SOT-23 Packaging Information |                         |            |
|------------------------------|-------------------------|------------|
| Packaging Option             | Standard (no flow code) | D87Z       |
| Packaging type               | TNR                     | TNR        |
| Qty per Reel/Tube/Bag        | 3,000                   | 10,000     |
| Reel Size                    | 7" Dia                  | 13"        |
| Box Dimension (mm)           | 187x107x183             | 343x343x64 |
| Max qty per Box              | 24,000                  | 30,000     |
| Weight per unit (gm)         | 0.0082                  | 0.0082     |
| Weight per Reel (kg)         | 0.1175                  | 0.4006     |
| Note/Comments                |                         |            |

### SOT-23 Unit Orientation

343mm x 342mm x 64mm  
Intermediate box for L87Z Option

Human Readable Label


Human Readable Label sample



Human readable Label

187mm x 107mm x 183mm  
Intermediate Box for Standard Option


**SOT-23 Tape Leader and Trailer Configuration:** Figure 20



## SOT-23 Tape and Reel Data, continued


### SOT-23 Embossed Carrier Tape

Configuration: Figure 3.0




| Dimensions are in millimeter |                 |                 |               |                 |                   |                 |             |                 |               |               |                 |                   |               |                 |
|------------------------------|-----------------|-----------------|---------------|-----------------|-------------------|-----------------|-------------|-----------------|---------------|---------------|-----------------|-------------------|---------------|-----------------|
| Pkg type                     | A0              | B0              | W             | D0              | D1                | E1              | E2          | F               | P1            | P0            | K0              | T                 | Wc            | Tc              |
| SOT-23 (8mm)                 | 3.15<br>+/-0.10 | 2.77<br>+/-0.10 | 8.0<br>+/-0.3 | 1.55<br>+/-0.05 | 1.125<br>+/-0.125 | 1.75<br>+/-0.10 | 6.25<br>min | 3.50<br>+/-0.05 | 4.0<br>+/-0.1 | 4.0<br>+/-0.1 | 1.30<br>+/-0.10 | 0.228<br>+/-0.013 | 5.2<br>+/-0.3 | 0.06<br>+/-0.02 |


Notes: A0, B0, and K0 dimensions are determined with respect to the EIA/Jedec RS-481 rotational and lateral movement requirements (see sketches A, B, and C).



Sketch A (Side or Front Sectional View)  
Component Rotation




Sketch B (Top View)  
Component Rotation



Sketch C (Top View)  
Component lateral movement

### SOT-23 Reel Configuration: Figure 4.0





| Dimensions are in inches and millimeters |             |               |              |                                   |               |             |                                   |               |                             |
|------------------------------------------|-------------|---------------|--------------|-----------------------------------|---------------|-------------|-----------------------------------|---------------|-----------------------------|
| Tape Size                                | Reel Option | Dim A         | Dim B        | Dim C                             | Dim D         | Dim N       | Dim W1                            | Dim W2        | Dim W3 (LSL-USL)            |
| 8mm                                      | 7" Dia      | 7.00<br>177.8 | 0.059<br>1.5 | 512 +0.020/-0.008<br>13 +0.5/-0.2 | 0.795<br>20.2 | 2.165<br>55 | 0.331 +0.059/-0.000<br>8.4 +1.5/0 | 0.567<br>14.4 | 0.311 - 0.429<br>7.9 - 10.9 |
| 8mm                                      | 13" Dia     | 13.00<br>330  | 0.059<br>1.5 | 512 +0.020/-0.008<br>13 +0.5/-0.2 | 0.795<br>20.2 | 4.00<br>100 | 0.331 +0.059/-0.000<br>8.4 +1.5/0 | 0.567<br>14.4 | 0.311 - 0.429<br>7.9 - 10.9 |

## SOT-23 Package Dimensions




### SOT-23 (FS PKG Code 49)



Scale 1:1 on letter size paper

Dimensions shown below are in:  
inches [millimeters]

Part Weight per unit (gram): 0.0082




NOTE : UNLESS OTHERWISE SPECIFIED

1. STANDARD LEAD FINISH 150 MICROINCHES / 3.81 MICROMETERS  
MINIMUM TIN / LEAD (SOLDER) ON ALLOY 42
2. REFERENCE JEDEC REGISTRATION TO-236, VARIATION AB, ISSUE G, DATED JUL 1993

## SOT-223 Tape and Reel Data



### SOT-223 Packaging Configuration: Figure 1.0




#### Packaging Description:


SOT-223 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 2,500 units per 13" or 330cm diameter reel. The reels are dark blue in color and is made of polystyrene plastic (anti-static coated). Other option comes in 500 units per 7" or 177cm diameter reel. This and some other options are further described in the Packaging Information table.

These full reels are individually barcode labeled and placed inside a standard intermediate box (illustrated in figure 1.0) made of recyclable corrugated brown paper. One box contains two reels maximum. And these boxes are placed inside a barcode labeled shipping box which comes in different sizes depending on the number of parts shipped.



| SOT-223 Packaging Information |                         |            |
|-------------------------------|-------------------------|------------|
| Packaging Option              | Standard (no flow code) | D84Z       |
| Packaging type                | TNR                     | TNR        |
| Qty per Reel/Tube/Bag         | 2,500                   | 500        |
| Reel Size                     | 13" Dia                 | 7" Dia     |
| Box Dimension (mm)            | 343x64x343              | 184x187x47 |
| Max qty per Box               | 5,000                   | 1,000      |
| Weight per unit (gm)          | 0.1246                  | 0.1246     |
| Weight per Reel (kg)          | 0.7250                  | 0.1532     |
| Note/Comments                 |                         |            |




#### SOT-223 Unit Orientation




343mm x 342mm x 64mm  
Intermediate box for Standard



#### F63TNR Label sample



### SOT-223 Tape Leader and Trailer Configuration: Figure 2.0







## SOT-223 Package Dimensions




### SOT-223 (FS PKG Code 47)



Scale 1:1 on letter size paper

Part Weight per unit (gram): 0.1246



NOTES : UNLESS OTHERWISE SPECIFIED

1. STANDARD LEAD FINISH TO BE 150 MICRONS/ 3.81 MICROMETERS

MINIMUM TIN/LEAD (SOLDER) ON COPPER.

2. REFERENCE JEDEC REGISTRATION TO-261, VARIATION AA, ISSUE A, DATED JAN 1990

SOT223, 4 LEADS

## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

|                                  |                                 |                                 |                        |
|----------------------------------|---------------------------------|---------------------------------|------------------------|
| ACE <sup>™</sup>                 | FAST <sup>™</sup>               | PowerTrench <sup>®</sup>        | SyncFET <sup>™</sup>   |
| Bottomless <sup>™</sup>          | GlobalOptoisolator <sup>™</sup> | QFET <sup>™</sup>               | TinyLogic <sup>™</sup> |
| CoolFET <sup>™</sup>             | GTO <sup>™</sup>                | QS <sup>™</sup>                 | UHC <sup>™</sup>       |
| CROSSVOLT <sup>™</sup>           | HiSeC <sup>™</sup>              | QT Optoelectronics <sup>™</sup> | VCX <sup>™</sup>       |
| DOVE <sup>™</sup>                | ISOPLANAR <sup>™</sup>          | Quiet Series <sup>™</sup>       |                        |
| E <sup>2</sup> CMOS <sup>™</sup> | MICROWIRE <sup>™</sup>          | SILENT SWITCHER <sup>®</sup>    |                        |
| EnSigna <sup>™</sup>             | OPTOLOGIC <sup>™</sup>          | SMART START <sup>™</sup>        |                        |
| FACT <sup>™</sup>                | OPTOPLANAR <sup>™</sup>         | SuperSOT <sup>™</sup> -3        |                        |
| FACT Quiet Series <sup>™</sup>   | PACMAN <sup>™</sup>             | SuperSOT <sup>™</sup> -6        |                        |
| FAST <sup>®</sup>                | POP <sup>™</sup>                | SuperSOT <sup>™</sup> -8        |                        |

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition                                                                                                                                                                                                            |
|--------------------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                                    |
| Preliminary              | First Production       | This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.                                                       |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.                                                   |