

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




以太网交换机，8个TP-RJ45端口，所有端口速率均为10/100/1000 Mbps，10/100/1000 Mbps (RJ45) 传输速率自动检测，自动交叉功能，带信号触点和QoS，温度范围广

优势

- ✓ 自适应与自交叉检测简化了安装和设置
- ✓ 开关也可进行电缆锁定和端口封闭
- ✓ 本地诊断指示，带LED
- ✓ 电压状态的报警继电器触点
- ✓ 所有端口的传输速度高达1000 Mbps

关键商业数据

包装单位	1 STK
GTIN	 4 046356 101172
GTIN	4046356101172
海关税则号	8486901000
Sales Key	DNN113

技术数据

注意

使用限制	EMC : A类产品，参见下载区内的制造商声明
------	-------------------------

尺寸

宽度	50 mm
高度	120 mm
深度	70 mm

环境条件

保护等级	IP20
环境温度 (运行)	-40 °C ... 75 °C
环境温度 (存放/运输)	-40 °C ... 85 °C

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

技术数据

环境条件

允许湿度 (运行)	5 % ... 95 % (无冷凝)
允许湿度 (存放/运输)	5 % ... 95 % (无冷凝)
空气压力 (运行)	86 kPa ... 108 kPa (最高可达海拔1500米)
空气压力 (存放/运输)	66 kPa ... 108 kPa (最高可达海拔3500米)

接口

接口	以太网 (RJ45)
端口数	8 (RJ45端口)
连接方法方面的注意事项	自适应和自交叉
传输原理	以太网RJ45双绞线
传输速度	10/100/1000 Mbps
接口	自由电位信号接点
连接方式	采用COMBICON直插式/螺钉连接

功能

基本功能	非管理型交换机/自适应, 遵循IEEE802.3, 存储和转发交换模式
其他功能	Autonegotiation
PROFINET一致性等级	Conformance-Class A
诊断和状态指示灯	LED: U_{S1} , U_{S2} (冗余电源电压), 各端口的链接和活动
信号触点控制电压	冗余电源电压监控

网络扩展参数

级联深度	网络、线型和星型结构: 任意
最大导线长度 (双绞线)	100 m

电源电压

电源电压	24 V DC (冗余)
残波	3.6 V _{pp} (在允许的电压范围内)
电源电压范围	9 V DC ... 32 V DC
典型电流耗量	430 mA ($U_S = 24$ V DC)

概述

安装类型	DIN导轨
类型AX	端子化设计
净重	395 g
外壳材料	铝

标准和规范

电磁兼容性	符合EMC 条例2004/108/EC
发射干扰	EN 61000-6-4
抗干扰	EN 61000-6-2:2005
振动 (存放/运输)	5g, 150 Hz, 符合EN 60068-2-6
振动 (操作)	符合IEC 60068-2-6: 5g, 150 Hz
符合性	符合 CE 标准

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

技术数据

标准和规范

UL , 美国 / 加拿大	Class I, Div. 2, Groups A, B, C, D
---------------	------------------------------------

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	环保使用期限 = 10 ;
	更多有害物质的详情, 请参考“下载区”内的“制造商声明”

分类

eCl@ss

eCl@ss 10.0.1	19170402
eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734
ETIM 7.0	EC000734

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612

认证

认证

认证

UL Listed / cUL Listed / EAC / EAC / KC / cULus Listed

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

认证

防爆认证

UL Listed / cUL Listed / cULus Listed

认证详情

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	--	---	---------------

EAC			EAC-Zulassung
-----	--	--	---------------

EAC			RU *- DE.A*30.B.01735
-----	--	--	--------------------------

KC		http://eng.kcc.go.kr/user/ehpMain.do	MSIP-REI- PCK-2891673
----	--	---	--------------------------

cULus Listed			
--------------	--	--	--

附件

附件

保护盖

防尘 - FL RJ45 PROTECT CAP - 2832991



RJ45 孔式连接器的防尘盖

安全锁定

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

附件

端口防护锁定元件 - FL SEC PAC 4TX - 2832865

第1层安全防护元件，用于配线箱和面板上的四个RJ45网络连接



尾缆

尾缆 - FL CAT5 PATCH 0,3 - 2832250



电缆，CAT5，已装配，0.3m

尾缆 - FL CAT5 PATCH 0,5 - 2832263



尾缆，CAT5，预装，0.5m

尾缆 - FL CAT5 PATCH 1,0 - 2832276



尾缆，CAT5，预装，1 m

尾缆 - FL CAT5 PATCH 1,5 - 2832221



尾缆，CAT5，预装，1.5m

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

附件

尾缆 - FL CAT5 PATCH 2,0 - 2832289



尾缆, CAT5, 预装, 2 m

尾缆 - FL CAT5 PATCH 3,0 - 2832292



尾缆, CAT5, 预装, 3 m

尾缆 - FL CAT5 PATCH 5,0 - 2832580



尾缆, CAT5, 预制, 5 m

尾缆 - FL CAT5 PATCH 7,5 - 2832616



尾缆, CAT5, 预装, 7.5 m

尾缆 - FL CAT5 PATCH 10,0 - 2832629



尾缆, CAT5, 预制, 10 m

末端

Industrial Ethernet Switch - FL SWITCH SFN 8GT - 2891673

附件

终端固定件 - E/NS 35 N - 0800886



终端固定件，宽度：9.5 mm，颜色：灰色

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>