



# Sonic-FRD

High Performance Fast Recovery Diode  
Low Loss and Soft Recovery  
Single Diode

$$\begin{aligned} V_{RRM} &= 600 \text{ V} \\ I_{FAV} &= 10 \text{ A} \\ t_{rr} &= 35 \text{ ns} \end{aligned}$$

Part number (Marking on product)

DHG 10 I 600PA



## Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low  $I_{RM}$ -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low  $I_{RM}$  reduces:
  - Power dissipation within the diode
  - Turn-on loss in the commutating switch

## Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

## Package:

- TO-220AC
- Industry standard outline
- Epoxy meets UL 94V-0
- RoHS compliant

## Ratings


| Symbol     | Definition                          | Conditions                                                                                                                                                  | min. | typ. | max.         | Unit                |
|------------|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|--------------|---------------------|
| $V_{RRM}$  | max. repetitive reverse voltage     | $T_{VJ} = 25^\circ\text{C}$                                                                                                                                 |      |      | 600          | V                   |
| $I_R$      | reverse current                     | $V_R = 600 \text{ V}$<br>$T_{VJ} = 25^\circ\text{C}$<br>$V_R = 600 \text{ V}$<br>$T_{VJ} = 125^\circ\text{C}$                                               |      |      | 15<br>1.5    | $\mu\text{A}$<br>mA |
| $V_F$      | forward voltage                     | $I_F = 10 \text{ A}$<br>$I_F = 20 \text{ A}$<br>$T_{VJ} = 25^\circ\text{C}$<br>$I_F = 10 \text{ A}$<br>$I_F = 20 \text{ A}$<br>$T_{VJ} = 125^\circ\text{C}$ |      |      | 2.35<br>2.20 | V<br>V<br>V<br>V    |
| $I_{FAV}$  | average forward current             | rectangular, $d = 0.5$<br>$T_C = 95^\circ\text{C}$                                                                                                          |      |      | 10           | A                   |
| $V_{FO}$   | threshold voltage                   | } for power loss calculation only<br>$T_{VJ} = 150^\circ\text{C}$                                                                                           |      |      | 1.20         | V                   |
| $r_F$      | slope resistance                    |                                                                                                                                                             |      |      | 93           | m $\Omega$          |
| $R_{thJC}$ | thermal resistance junction to case |                                                                                                                                                             |      |      | 1.80         | K/W                 |
| $T_{VJ}$   | virtual junction temperature        |                                                                                                                                                             | -55  |      | 150          | $^\circ\text{C}$    |
| $P_{tot}$  | total power dissipation             | $T_C = 25^\circ\text{C}$                                                                                                                                    |      |      | 70           | W                   |
| $I_{FSM}$  | max. forward surge current          | $t_p = 10 \text{ ms (50 Hz), sine}$<br>$T_{VJ} = 45^\circ\text{C}$                                                                                          |      |      | 100          | A                   |
| $I_{RM}$   | max. reverse recovery current       | $I_F = 10 \text{ A};$<br>$-di_F/dt = 200 \text{ A}/\mu\text{s}$<br>$T_{VJ} = 25^\circ\text{C}$<br>$T_{VJ} = 125^\circ\text{C}$                              |      | 4    |              | A<br>A              |
| $t_{rr}$   | reverse recovery time               | $V_R = 400 \text{ V}$<br>$T_{VJ} = 25^\circ\text{C}$<br>$T_{VJ} = 125^\circ\text{C}$                                                                        |      | 35   |              | ns<br>ns            |
| $C_j$      | junction capacitance                | $V_R = 300 \text{ V}; f = 1 \text{ MHz}$<br>$T_{VJ} = 25^\circ\text{C}$                                                                                     |      |      |              | pF                  |
| $E_{AS}$   | non-repetitive avalanche energy     | $I_{AS} = \text{A}; L = 100 \mu\text{H}$<br>$T_{VJ} = 25^\circ\text{C}$                                                                                     |      |      | tbd          | mJ                  |
| $I_{AR}$   | repetitive avalanche current        | $V_A = 1.5 \cdot V_R \text{ typ.}; f = 10 \text{ kHz}$                                                                                                      |      |      | tbd          | A                   |

| Symbol     | Definition                          | Conditions | Ratings |      |      | Unit |
|------------|-------------------------------------|------------|---------|------|------|------|
|            |                                     |            | min.    | typ. | max. |      |
| $I_{RMS}$  | RMS current                         | per pin*   |         |      | 35   | A    |
| $R_{thCH}$ | thermal resistance case to heatsink |            |         | 0.50 |      | K/W  |
| $M_D$      | mounting torque                     |            | 0.4     |      | 0.6  | Nm   |
| $F_C$      | mounting force with clip            |            | 20      |      | 60   | N    |
| $T_{stg}$  | storage temperature                 |            | -55     |      | 150  | °C   |
| Weight     |                                     |            |         | 2    |      | g    |

\*  $I_{rms}$  is typically limited by: 1. pin-to-chip resistance; or by 2. current capability of the chip.

In case of 1, a common cathode/anode configuration and a non-isolated backside, the whole current capability can be used by connecting the backside.

## Outlines TO-220AC



| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 12.70      | 14.73 | 0.500  | 0.580 |
| B    | 14.23      | 16.51 | 0.560  | 0.650 |
| C    | 9.66       | 10.66 | 0.380  | 0.420 |
| D    | 3.54       | 4.08  | 0.139  | 0.161 |
| E    | 5.85       | 6.85  | 2.300  | 0.420 |
| F    | 2.54       | 3.42  | 0.100  | 0.135 |
| G    | 1.15       | 1.77  | 0.045  | 0.070 |
| H    | -          | 6.35  | -      | 0.250 |
| J    | 0.64       | 0.89  | 0.025  | 0.035 |
| K    | 4.83       | 5.33  | 0.190  | 0.210 |
| L    | 3.56       | 4.82  | 0.140  | 0.190 |
| M    | 0.51       | 0.76  | 0.020  | 0.030 |
| N    | 2.04       | 2.49  | 0.080  | 0.115 |
| Q    | 0.64       | 1.39  | 0.025  | 0.055 |