




RIGHT ANGLE PLUG CRIMP TYPE

CABLE 5/50 S

R125.176.001

Series : SMA



All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING
BODY	STAINLESS STEEL	PASSIVATED . μm
CENTRE CONTACT	BRASS	GOLD 0.5 OVER NICKEL 2 μm
OUTER CONTACT	-	- μm
INSULATOR	PTFE	
GASKET	SILICONE RUBBER	
OTHERS PARTS	STAINLESS STEEL	PASSIVATED . μm
-	-	-
-	-	-



Edition : 9840 M

Design changes may be in order to improve the product.

RIGHT ANGLE PLUG CRIMP TYPE**R125.176.001****CABLE 5/50 S**Series : **SMA****ELECTRICAL CHARACTERISTICS**

Impedance	50 Ω
Frequency	0-12.4 GHz
VSWR	1.15 + 0.020 x F(GHz) Maxi
Insertion loss	0.15 √F(GHz) dB
RF leakage	- (60 - F(GHz)) dB mini
Operating temperature	-65/+165 °C
Voltage rating	335 Veff Maxi
Dielectric withstanding	1000 Veff mini
Insulation resistance	5000 MΩ mini

SPECIFICATION

Stripping	a	b	c	d	e	f
mm	2.80	7.00	12.8	0.00	10.0	0.00

Assembly instruction : **Crimp 04**

Recommended cables

RG 223
RG 142
RG 400
KX 23
RG 142 FTX

Cable retention

- pull off **204** N mini
- torque **NA** N.cm

MECHANICAL CHARACTERISTICS

Centre contact retention	
Axial force – Mating end	27 N mini
Axial force – Opposite end	27 N mini
Torque	2.8 N.cm mini

TOOLING

Part Number	Description	Hexagon
.	.	.
R282.223.000	CRIMPING TOOL	5.40
R282.235.011	CRIMPING DIES	5.40
R282.293.000	CRIMPING TOOL	-

Recommended torque

Mating	100 N.cm
Panel nut	NA N.cm
Clamp nut	NA N.cm
A/F clamp nut	0.000 mm

Mating life	500 Cycles mini
Weight	0.000 g

OTHERS CHARACTERISTICS

-

ENVIRONMENTAL

Hermetic seal	NA Atm.cm3/s
Leakage – pressurised only	NA Mpa

Edition : **9840 M**

Design changes may be in order to improve the product.