



### Main

Range of product	Acti 9
Modular device name	IHP
Device short name	IHP 1c 18 mm
Product or component type	Programmable digital time switch
Number of channels	1
Battery type	Lithium
Function available	Operating hours counter Automatic winter/summer time changeover
Type of setting	Absence for holidays function PIN code
Provided equipment	Memory key Programming kit
Language	Dutch English French Italian Portuguese Spanish

### Complementary

Device application	Building
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min
Accuracy	+/- 0.5 s/day 25 °C
Power consumption	0.4 W
Maximum switching current	4 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] rated operational voltage	230 V ( +10 % -15 % ) AC 50/60 Hz
Display type	LCD
Battery life	10 yr
Backup time	10 years time and program saving
Product mounting	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screwless terminals : 2 x 0.5...2.5 mm <sup>2</sup>
Width	18 mm
Height	90 mm
Depth	66 mm
Product weight	90 g

### Environment

Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP20 B

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.