

Interface module - VIP-2/PT/D15SUB/M - 2903779


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 15-pos.



Key commercial data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| GTIN |  4 046356 796545 |
| Weight per Piece (excluding packing) | 116.3 g |
| Custom tariff number | 85369010 |
| Country of origin | United States |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|--------|---------|
| Width | 46.9 mm |
| Height | 72.1 mm |
| Depth | 63 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|------------------------------------|--------------|
| Max. permissible operating voltage | 125 V AC/DC |
| Max. perm. current (per branch) | 2 A |
| Number of positions | 15 |
| Status display | No |
| Mounting position | any |
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |
| | IEC 62103 |

Interface module - VIP-2/PT/D15SUB/M - 2903779

Technical data

General

| | |
|------------------------|--------|
| Rated surge voltage | 1.2 kV |
| Pollution degree | 2 |
| Surge voltage category | II |

Connection data for connection 1

| | |
|--|----------------------|
| Connection name | PCB connection |
| Connection method | Push-in connection |
| Conductor cross section solid min. | 0.14 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section stranded min. | 0.14 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 26 |
| Conductor cross section AWG/kcmil max. | 14 |
| Stripping length | 8 mm |

Connection data for connection 2

| | |
|-----------------------|------------------|
| Connection name | D-SUB connection |
| Number of connections | 1 |
| Connection method | D-SUB pin strip |
| Number of positions | 15 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27371001 |
| eCl@ss 4.1 | 27371001 |
| eCl@ss 5.0 | 27371001 |
| eCl@ss 5.1 | 27371001 |
| eCl@ss 6.0 | 27371001 |
| eCl@ss 7.0 | 27371001 |
| eCl@ss 8.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001604 |
| ETIM 4.0 | EC000196 |
| ETIM 5.0 | EC002780 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211916 |
| UNSPSC 7.0901 | 39121515 |
| UNSPSC 11 | 39121515 |
| UNSPSC 12.01 | 39121542 |

Interface module - VIP-2/PT/D15SUB/M - 2903779

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121515 |
|-------------|----------|

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

| | |
|--------------------------------|-------|
| CSA | |
| mm ² /AWG/kcmil | 26-14 |
| Nominal current I _N | 2 A |
| Nominal voltage U _N | 105 V |

| | |
|--------------------------------|-------|
| UL Recognized | |
| mm ² /AWG/kcmil | 26-14 |
| Nominal current I _N | 2 A |
| Nominal voltage U _N | 125 V |

| | |
|--------------------------------|-------|
| cUL Recognized | |
| mm ² /AWG/kcmil | 26-14 |
| Nominal current I _N | 2 A |
| Nominal voltage U _N | 125 V |

Interface module - VIP-2/PT/D15SUB/M - 2903779

Approvals

EAC

cULus Recognized  US

Accessories

Accessories

Printing system

Printer - BLUEMARK X1 - 5147777



Printers with UV technology for printing plastic labels in UniCard format.

System cable

Cable - CABLE-D15SUB/B/S/ 50/KONFEK/S - 2302052



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 0.5 m

Cable - CABLE-D15SUB/B/S/100/KONFEK/S - 2302065



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 1 m

Cable - CABLE-D15SUB/B/S/150/KONFEK/S - 2302078



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 1.5 m

Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

Cable - CABLE-D15SUB/B/S/200/KONFEK/S - 2302081



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 2 m

Cable - CABLE-D15SUB/B/S/300/KONFEK/S - 2302094



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 3 m

Cable - CABLE-D15SUB/B/S/400/KONFEK/S - 2302104



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 4 m

Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 6 m

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

Cable - CABLE-D15SUB/B/B/100/KONFEK/S - 2305444



Assembled, shielded circular cable, with D-SUB socket strip, 15-pos. from both sides, cable length: 1 m

Cable - CABLE-D15SUB/B/B/200/KONFEK/S - 2305457



Assembled, shielded circular cable, with D-SUB socket strip, 15-pos. from both sides, cable length: 2m

Cable - CABLE-D15SUB/B/B/300/KONFEK/S - 2305460



Assembled, shielded circular cable, with D-SUB socket strip, 15-pos. from both sides, cable length: 3 m

Cable - CABLE D-SUB-B-B-S/.../.../... - 2302421



Shielded round cable, assembled with two D-SUB female connectors, variable cable length

Terminal marking

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

Drawings

Circuit diagram

