

10

9

8

7

6

5

4

3

2




1

MAT'L NO.

ENG NO.

15-24-4742

A-8981-4V6-LF



NOTES :

1. PLATING
POSTPLATE 0.00254/.000100 MIN. TIN
OVER 0.00127/.000050 MIN. NICKEL OVERALL.
2. PART TO MATE WITH HOUSING 8981-4P2
AND TERMINAL 8980-3*.
3. PRODUCT SPEC PS-8981-4V4/4R1-P APPLIES.
4. MATERIAL:
HOUSING - PCT, GLASS FILLED, UL94V-0
COLOR BLACK
TERMINAL - PHOS BRONZE

ADD CKT INDICATION	
EC NO: S2009-0836	2009/05/08
DRWN:SKANG	2009/05/08
CHKD:ATSEE	2009/05/11
APPR:MLONG	2009/05/11
REV	DESCRIPTION
D1	

QUALITY SYMBOLS
$\nabla = 0$
$\nabla = 0$

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES $\pm$ ---	$\pm$ ---
3 PLACES $\pm$ ---	$\pm$.008
2 PLACES $\pm$ 0.20	$\pm$ ---
1 PLACE $\pm$ ---	$\pm$ ---
ANGULAR $\pm$ 3 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
SKTOH	1991/10/17
CHECKED BY	DATE
GWANG	1991/11/14
APPROVED BY	DATE
RWONG	1991/11/14
MATERIAL NO.	
SEE TABLE	
SIZE	
A3	

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
NTS	METRIC	
TITLE		
POWER CONNECTOR, 4 CKTS VERTICAL MOUNT		
MOLEX INCORPORATED		
DOCUMENT NO.		SHEET NO.
SD-8981-4V6		1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

9

8

7

6

5

4

3

2

1