


NO	DESCRIPTION	DATE
⚠	MODIFY TAPE AND REEL PACKAGING	07.08.10



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-6 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 170 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 500 VOLTS
- 1.5 VSWR: 1.5 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
BERYLLIUM COPPER PER ASTM B198 UNS C17500
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: BS EN 122340

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -55° C TO +155° C

8	CENTER CONTACT III	BRASS	1	GOLD 3μ" MIN.
7	INSULATION III	TEFLON	1	NONE
6	SPRING	STAINLESS STEEL	1	NONE
5	CENTER CONTACT II	BRASS	1	GOLD 3μ" MIN.
4	INSULATION II	TEFLON	1	NONE
3	INSULATION I	TEFLON	1	NONE
2	CENTER CONTACT I	BERYLLIUM COPPER	1	GOLD 30μ" MIN.
1	BODY	BRASS	1	GOLD 3μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED by _____ DATE: _____

DESCRIPTION		MMCX STRAIGHT EDGE MOUNT JACK SWITCHING									
製圖	DRAWN	TOLERANCE		品名	37-18-1 T.G.G		日期	DATE	版次	REV.	
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT (500)			05.26.10			A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO. 37-0078					
	Arc	.XXX	±0.05		mm(in)						
認定	APPROVAL	ANGLE	±5°	比例	SCALE						
	Lewis				8:1						

