

Burrs

Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro


Cone

Spitzkegelform
Conique
Cono



d1 mm	3	3	6	6	6	10
l1 mm	11	16	13	13	19	16
d2 mm	3	3	3	6	6	6
l2 mm	38	38	45	50	50	65
s	GT2200	GT2220	GT2240	-	GT2400	-
d	GT2200D	GT2220D	GT2240D	GT2300D	GT2400D	GT2400D-1
d-max™	-	-	-	-	-	-
c	-	-	-	-	-	GT2600C
k	GT2200K	-	-	-	GT2400K	-
alu	-	-	-	-	-	-
I.S.O. Ref.	M031103	M031603	M061303	M061306	M061906	M062506
SCTI Nr.	SM-42M	SM-43M	SM-51M	SM-1M	SM-2M	SM-3M
IPC Code	49	49	49	25	25	25

d1 mm	12	12	12	16	16
l1 mm	19	25	25	25	25
d2 mm	6	6	8	6	8
l2 mm	65	70	70	73	73
s	GT2700	GT2700-1	GT2700-1-8	-	-
d	GT2700D	GT2700D-1	GT2700D-1-8	GT2750D-1-6	GT2750D-1
d-max™	-	-	-	-	-
c	-	GT2700C-1	-	-	-
k	-	GT2700K-1	-	-	-
alu	-	-	-	-	-
I.S.O. Ref.	M121906	M122206	M122208	M162206	M162208
SCTI Nr.	SM-13M	SM-5M	SM-5M8	SM-6M	SM-6M8
IPC Code	25	25	25	25	25





Burrs

Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro

RAPIDE® Coated burrs - Cone

RAPIDE® Spitzkegelform
RAPIDE® Conique
RAPIDE® Cono



d1 mm	3	3	6	6	6	10
l1 mm	11	16	13	13	19	16
d2 mm	3	3	3	6	6	6
l2 mm	38	38	45	50	50	65
s	GCZ2200	GCZ2220	GCZ2240	-	GCZ2400	-
d	GCZ2200D	GCZ2220D	GCZ2240D	GCZ2300D	GCZ2400D	GCZ2400D-1
d-max™	-	-	-	-	-	-
c	-	-	-	-	-	GCZ2600C
k	GCZ2200K	-	-	-	GCZ2400K	-
alu	-	-	-	-	-	-
I.S.O. Ref.	M031103	M031603	M061303	M061306	M061906	M062506
SCTI Nr.	SM-42M	SM-43M	SM-51M	SM-1M	SM-2M	SM-3M
IPC Code	22	22	22	22	22	22

d1 mm	12	12	12	16	16
l1 mm	19	25	25	25	25
d2 mm	6	6	8	6	8
l2 mm	65	70	70	73	73
s	GCZ2700	GCZ2700-1	GCZ2700-1-8	-	-
d	GCZ2700D	GCZ2700D-1	GCZ2700D-1-8	GCZ2750D-1-6	GCZ2750D-1
d-max™	-	-	-	-	-
c	-	GCZ2700C-1	-	-	-
k	-	GCZ2700K-1	-	-	-
alu	-	-	-	-	-
I.S.O. Ref.	M121906	M122206	M122208	M162206	M162208
SCTI Nr.	SM-13M	SM-5M	SM-5M8	SM-6M	SM-6M8
IPC Code	22	22	22	22	22



d1 mm	3	3	6	6	6	10
l1 mm	11	16	13	13	19	16
d2 mm	3	3	3	6	6	6
l2 mm	38	38	45	50	50	65
s	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	-	RAPIDE®-D	-
d	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
d-max™	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
c	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
k	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
alu	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A
I.S.O. Ref.	M031103	M031603	M061303	M061306	M061906	M062506
SCTI Nr.	SM-42M	SM-43M	SM-51M	SM-1M	SM-2M	SM-3M
IPC Code	49	49	49	25	25	25

d1 mm	12	12	12	16	16
l1 mm	19	25	25	25	25
d2 mm	6	6	8	6	8
l2 mm	65	70	70	73	73
s	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	-	-
d	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
d-max™	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
c	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
k	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D	RAPIDE®-D
alu	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A	RAPIDE®-A
I.S.O. Ref.	M121906	M122206	M122208	M162206	M162208
SCTI Nr.	SM-13M	SM-5M	SM-5M8	SM-6M	SM-6M8
IPC Code	25	25	25	25	25

Additional lead times may apply on coated burrs.
Längere Lieferzeiten dürfen mit beschichteten Hartmetallfrässtiften gelten.

Délais de livraison peuvent être plus longs pour les fraises limes revêtues.
Las fresas recubiertas pueden tener un plazo de entrega más largo.