

Datasheet

**RS Pro 3 → 28 V dc 89dB sound SMD Continuous Internal Piezo Buzzer, 2300 → 3300 Hz**

RS Stock No: **754-2012**



## Product Details

RS Pro internal piezo buzzer operates at a voltage range of 3 - 28 V dc. This continuous, SMD buzzer delivers 89 dB sound at a frequency range of 2300 - 3300 Hz. It is suitable for applications that require high sound output.

## Features and Benefits

- Circular cased PCB mounting
- High sound output buzzers
- Continuous delivery

**Specifications:**

|                               |                   |
|-------------------------------|-------------------|
| Drive Type                    | Internal          |
| Mounting Type                 | Surface Mount     |
| Tone Type                     | Continuous        |
| Diameter                      | 42 mm             |
| Dimensions                    | 42 (dia.) x 14 mm |
| Height                        | 14 mm             |
| Maximum Frequency             | 3300 Hz           |
| Maximum Operating Temperature | +85°C             |
| Maximum Supply Voltage        | 28 V dc           |
| Minimum Frequency             | 2300 Hz           |
| Minimum Operating Temperature | -30°C             |
| Minimum Supply Voltage        | 3 V dc            |
| Sound Level                   | 89 dB             |
| Supply Current                | 10 mA             |