


## Diode block - EMG 45-DIO 8E/LP - 2954798

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Lamp test module, 2 diodes with common cathode: with 4 pairs, for individual wiring



### Key commercial data

Packing unit	5 pc
GTIN	 4 017918 085131
Weight per Piece (excluding packing)	82.7 g
Custom tariff number	85411000
Country of origin	Germany

### Technical data

#### Dimensions

Width	45 mm
Height	75 mm
Depth	55 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

#### General

Max. operating voltage	250 V AC
Peak reverse voltage per diode	1300 V
Reverse current per diode	≤ 5 µA
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	0.7 A (with single load)
	0.4 A (with simultaneous loads)
Pollution degree	2

# Diode block - EMG 45-DIO 8E/LP - 2954798

## Technical data

### General

Surge voltage category	III, basic insulation (as per EN 50178)
Mounting position	any
Assembly instructions	In rows with zero spacing

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

## Classifications

### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27260801
eCl@ss 5.0	27260801
eCl@ss 5.1	27260801
eCl@ss 6.0	27242602
eCl@ss 7.0	27242602
eCl@ss 8.0	27242602

### ETIM

ETIM 2.0	EC001432
ETIM 3.0	EC001597
ETIM 4.0	EC001597
ETIM 5.0	EC001597

### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008

## Approvals

### Approvals

# Diode block - EMG 45-DIO 8E/LP - 2954798

## Approvals

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

## Approval details

GOST

## Accessories

Accessories

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

## Drawings

Circuit diagram

