

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40°C TO 85°C	STORAGE TEMPERATURE RANGE	-40°C TO 60°C
	VOLTAGE	125 V AC	OPERATING HUMIDITY RANGE	5 %RH TO 95 %RH
	CURRENT	No.2 TO No.17 : 0.5 A No.1 AND No. 18 : 1.5 A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	70 mΩ MAX.	X	—
INSULATION RESISTANCE	250 V DC.	1000 MΩ MIN.	X	—
VOLTAGE PROOF	350 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X

MECHANICAL CHARACTERISTICS				
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	25 N MAX.	X	—
MECHANICAL OPERATION	20,000 TIMES INSERTIONS AND EXTRACTIONS.	1) AMOUNT OF CHANGE OF CONTACT RESISTANCE : 20mΩ MAX 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 10μs. 2) AMOUNT OF CHANGE OF CONTACT RESISTANCE : 20mΩ MAX	X	—
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—


ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60°C , 90~95%, 96h	1) AMOUNT OF CHANGE OF CONTACT RESISTANCE : 20mΩ MAX	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → 5-35 → +85 → 5-35 °C TIME 30 → 2~3 → 30 → 2~3 min. UNDER 5 CYCLES.	2) INSULATION RESISTANCE: 1000 MΩ MIN. (AT DRY) 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION.	X	—
MIXED GAS CORROSION	EXPOSED IN SO ₂ 10 ppm , H ₂ S 3ppm 70 TO 80% R H. FOR 96 h			
RESISTANCE TO SOLDERING HEAT (REFLOW)	REFROUW TWICE UNDER THERECOMMENDED REFLOW TEMPERATURE PROFILE IN FIG-1	NO SIGNIFICANT DEFOMATION OR LOSSENESS OF CONTACTS.	X	—
RESISTANCE TO SOLDERING. SOLDER IRON METHOD	TEMPERATURE OF SOLDERING IRON : 390°C MAX, 3 sec MAX	NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—

RECOMMENDED REFLOW PROFILE IN FIG-1

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				
REMARK			APPROVED	NF. MIYAZAKI 10.03.25
			CHECKED	TA. ASO 10.03.25
			DESIGNED	KO. KAWAMURA 10.03.25
Unless otherwise specified, refer to JIS C 5402.			DRAWN	KO. KAWAMURA 10.03.25

Note	QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC4-127060-00	
HRS	SPECIFICATION SHEET	PART NO.	3880-B-18P	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL238-2008-2-00	△ 1/2

ATTACHMENT FIGURE



Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO.

ELC4-127060-00



SPECIFICATION SHEET

PART NO.

3880-B-18P

HIROSE ELECTRIC CO., LTD.

CODE NO

CL238-2008-2-00



2/2