



mecalectro

## Electromagnet for retaining or handling parts – 5.81.01



**Diameter:** 39 mm

**Holding force when power on:** 44 daN

**Power Consumption:** 7.5 W

**Total mass:** 300 g

**Degree of protection / Energetic class:** IP 40 / B

**Standard supplies:** 24Vcc

**Possible supplies:** From 12 to 200Vcc

**Duty Cycle:** Permanent (100%)

**Standard:** NF C 79300

**Examples of applications:** Maintaining parts, blocking parts, positioning, gripping.