


Technical Data Sheet		Rosenberger																																			
BNC 75 Ω	STRAIGHT PLUG	71S106-009N5																																			
  All dimensions are in mm; tolerances according to ISO 2768 m-H <table><tr><th colspan="2">Interface</th></tr><tr><td>Compatible to</td><td>IEC 61169-8, MIL-PRF-39012, CECC 22120</td></tr><tr><th colspan="2">Documents</th></tr><tr><td>Assembly instruction</td><td>51 E</td></tr><tr><th colspan="3">Material and plating</th></tr><tr><th colspan="3">Connector parts</th></tr><tr><td>Center contact</td><td>Material</td><td>Plating</td></tr><tr><td>Outer contact</td><td>Brass</td><td>AuroDur®, gold plated</td></tr><tr><td>Body</td><td>Brass</td><td>Flash white bronze over silver(e.g. Optargen®)</td></tr><tr><td>Dielectric</td><td>Brass</td><td>Flash white bronze over silver(e.g. Optargen®)</td></tr><tr><td>Gasket</td><td>PTFE</td><td></td></tr><tr><td>Gasket</td><td>NeopreneCR 50C6</td><td></td></tr><tr><td>Gasket</td><td>Silicone</td><td></td></tr></table>			Interface		Compatible to	IEC 61169-8, MIL-PRF-39012, CECC 22120	Documents		Assembly instruction	51 E	Material and plating			Connector parts			Center contact	Material	Plating	Outer contact	Brass	AuroDur®, gold plated	Body	Brass	Flash white bronze over silver(e.g. Optargen®)	Dielectric	Brass	Flash white bronze over silver(e.g. Optargen®)	Gasket	PTFE		Gasket	NeopreneCR 50C6		Gasket	Silicone	
Interface																																					
Compatible to	IEC 61169-8, MIL-PRF-39012, CECC 22120																																				
Documents																																					
Assembly instruction	51 E																																				
Material and plating																																					
Connector parts																																					
Center contact	Material	Plating																																			
Outer contact	Brass	AuroDur®, gold plated																																			
Body	Brass	Flash white bronze over silver(e.g. Optargen®)																																			
Dielectric	Brass	Flash white bronze over silver(e.g. Optargen®)																																			
Gasket	PTFE																																				
Gasket	NeopreneCR 50C6																																				
Gasket	Silicone																																				
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de																																			
		Page 1 / 2																																			

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/08.13/6.1

Technical Data Sheet				Rosenberger			
BNC 75 Ω		STRAIGHT PLUG		71S106-009N5			
Electrical data Impedance75 Ω FrequencyDC to 4 GHz Return loss≥ 33 dB @ DC to 1 GHz ≥ 30 dB @ 1 GHz to 2 GHz ≥ 28 dB @ 2 GHz to 4 GHz Insertion loss≤ 0.05 x √ f [GHz] dB Insulation resistance≥ 5 GΩ Center contact resistance≤ 1.5 mΩ Outer contact resistance≤ 1 mΩ Test voltage (at sea level)1500 V rms Working voltage (at sea level)400 V rms Power handling (at 20 °C, sea level, VSWR 1.0)80 W @ 2 GHz - Limitations are possible due to the used cable type - Mechanical data Mating cycles≥ 500 Center contact captivation: axial≥ 15 N Environmental data Temperature range-65 °C to +165 °C Thermal shockMIL-STD-202, Method 107, Condition B Corrosion resistanceMIL-STD-202, Method 101, Condition B VibrationMIL-STD-202, Method 204, Condition B ShockMIL-STD-202, Method 213, Condition G Moisture resistanceMIL-STD-202, Method 106 RoHScompliant Tooling N/A Suitable cables RG 59 B/U Packing Standard1 pce in bag Weight16.0 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	03.08.04	A. Gasteiger	06.08.13	c00	07-0154	J. Krautenbacher	06.08.13
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de			Page 2 / 2