


DCO SD2 ME 24 (917 921)


- Space-saving terminal block with integrated surge protection
- Disconnection module for isolating signal circuits for maintenance work
- For installation in conformity with the lightning protection zones concept at the boundaries from $0_b - 2$ and higher



Figure without obligation



Basic circuit diagram DCO SD2 ME 24



Dimension drawing DCO SD2 ME 24

Energy coordinated two-stage arrester with disconnection function for protecting two single lines sharing a common reference potential as well as unbalanced interfaces.

Type Part No.	DCO SD2 ME 24 917 921
SPD class	TYPE 2 PG
Nominal voltage (U_N)	24 V
Max. continuous operating d.c. voltage (U_C)	33 V
Max. continuous operating a.c. voltage (U_C)	23 V
Nominal current at 80 °C (I_n)	0.5 A
C2 Total nominal discharge current (8/20 μ s) (I_n)	10 kA
C2 Nominal discharge current (8/20 μ s) per line (I_n)	5 kA
Voltage protection level line-line for I_n C2 (U_p)	≤ 120 V
Voltage protection level line-PG for I_n C2 (U_p)	≤ 75 V
Voltage protection level line-line at 1 kV/ μ s C3 (U_p)	≤ 90 V
Voltage protection level line-PG at 1 kV/ μ s C3 (U_p)	≤ 45 V
Series resistance per line	1.8 ohms
Cut-off frequency line-PG (f_c)	6 MHz
Capacitance line-line (C)	≤ 0.5 nF
Capacitance line-PG (C)	≤ 1.0 nF
Operating temperature range	-40°C...+80°C
Degree of protection	IP 00
For mounting on	35 mm DIN rails acc. to EN 60715
Connection (input/output)	spring / spring
Cross-sectional area (solid)	0.34 - 2.5 mm ²
Cross-sectional area (flexible)	0.34 - 2.5 mm ²
Earthing via	DIN rail / terminal
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Extended technical data:	-----
- Max. discharge current (8/20) [1/2 - PG], [1+2 - PG] (I_{max})	20 kA
- Voltage protection level line-PG at 1 kV/ μ s C3 after being subjected to I_{max} (U_p)	≤ 45 V
Weight	31 g
Customs tariff number	85363010
GTIN	4013364150577
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.