

NUMERO 790 319

DIBUJADO EN PROYECCIONES

AMERICANAS
EUROPEAS

REV

DESCRIPTION

DATE

DW

APPV

F1

REVISED PER ECO-10-000445

22JAN10

KK

HMR

G



SEE ECR-11-006271

25MAR11

JS


LB

SECCION B - B



SECCION A - A

SECCION C - C



1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2 WIRE CRIMP 6500 CMA MINIMUM

Tolerancia general $\pm 0,38 / \pm 1^\circ$

PLANO DE CLIENTE SOLO PARA REFERENCIA

790319-6	LATON	PLATEADO
790319-7	BRONCE FOSF.	PLATEADO
790319-6	BRONCE FOSF.	PLATEADO
790319-5	BRONCE FOSF.	PRE-ESTIÑADO
790319-4	BRONCE FOSF.	
790319-3	Latón	Pre-estañado

TE

TE Connectivity

GAMA HILO	GAMA AISLANTE	PRIMER USO
3,3 - 6 m/m ²	3A - 5,1 mm ²	

ESCALA	LOC	A	N.º	790 319	REV.	G
--------	-----	---	-----	---------	------	---

NOMBRE RECEPTACULO POSITIVE LOCK

COMP.	FECHA	REV.	FECHA
	16-9-80		4/5/81
	4/5/83	F 6500-0018-99	