


D

C

B

A



LC CONN. MARK		LC CONN. MARK
A	↔	B
B	↔	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2RETURN LOSS ≥ 25 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 850 nm
- 3TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4CABLE INFORMATION:


— CORE DIAMETER:50/125 μm

— OUTER JACKET DIAMETER:1.8x3.6 mm

— OUTER JACKET COLOUR:AQUA

— OUTER JACKET MATERIAL:LSZH
- 5BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	”L” (meter)
X-2061311-Y	XY.0

2	BLANK LABEL			3		
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE			2		
L	FOCAB 1.8MZ 50/125 OM3, AQUA, LSZH			1		
Qty	Description			Item		
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COOLEN 16OCT2009	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland		
DIMENSIONS: mm 		CHK A. HENGELMOLEN 16OCT2009	NAME FIBER OPTIC LEAD 1.8MZ LC/DPX – LC/DPX MULTI MODE 50/125 OM3			
		APVD A. HENGELMOLEN 16OCT2009				
		PRODUCT SPEC —				
MATERIAL —		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=2061311	RESTRICTED TO —
		WEIGHT —	CUSTOMER DRAWING			SCALE NTS