

Pico-ITX Series

VIA EPIA-P720

Pico-ITX Eden™ ULV Board
with MPEG-2, WMV9, H.264,
LVDS, HDMI, USB, SATA &
GigaLAN

Features

- Integrated VIA Chrome™9 HCM DX9 3D/2D graphics with MPEG-2, WMV9 & H.264 video decoding acceleration
- Supports DDR2 800/667 SDRAM (SODIMM), up to 2GB
- Supports one Gigabit Ethernet
- Supports one IDE and one SATA hard drive
- Supports six USB 2.0 ports
- Onboard LVDS support: One single-channel LVDS panel support
- Supports HD audio
- Supports one HDMI port



Board Placement


DC-in

VGA + USB pin connector

HDMI

LAN pin connector

IDE connector (2.0mm 44-pin)



DIO (4 GPI & 4 GPO) + SMBus + LPC pin connector

VIA Eden™ ULV processor

Front panel pin connector

VIA VX855 chipset

USB pin connector

SATA connector

Audio pin connector


SATA power

Specifications


Model Name	EPIA-P720-10EL
Processor	1.0GHz VIA Eden™ ULV
Chipset	VIA VX855 Unified Digital Media IGP chipset
System Memory	1 x DDR2 800/667 SODIMM socket Up to 2GB memory size
VGA	Integrated VIA Chrome™9 HCM DX9 3D/2D graphics with MPEG-2, WMV9 & H.264 video decoding acceleration
Onboard IDE	1 x IDE 2.0mm 44-pin pin header
Onboard Serial ATA	1 x SATA connector
Onboard LAN	1 x VIA VT6122 Gigabit Ethernet controller
Onboard Audio	1 x VIA VT1708B High Definition Audio Codec
Onboard I/O Connectors	1 x USB pin connector for 4 additional USB 2.0 ports 1 x LPC pin connector 1 x SMBus pin connector 1 x Front panel pin connector 1 x PS2 mouse/keyboard pin connector 1 x Fan pin connector: Sys FAN 1 x Single-channel LVDS pin connector (with backlight control) 1 x Audio pin connector for Line-out, & Mic-in 1 x DIO pin connector (4GPI+4GPO) 2 x UART port pin-header/VCP 1 x SATA power connector 1 x DC-in power connector
Back Panel I/O	1 x HDMI port 1 x VGA port 1 x GigaLAN port 2 x USB 2.0 ports
BIOS	AMI BIOS 4Mbit LPC flash memory
Operating System	Windows XP, Windows Embedded CE, Windows Embedded Standard, Linux
System Monitoring & Management	Wake-on LAN, Keyboard Power-on, Timer Power-on System power management, AC power failure recovery Watch Dog Timer
Operating Temperature	0°C ~ 60°C
Operating Humidity	0% ~ 95% (relative humidity; non-condensing)
Form Factor	Pico-ITX 10 cm x 7.2 cm (6.7" x 6.7")
Compliance	CE/FCC/BSMI/RoHS

Back Panel I/O


I/O of EPIA-P720 Board



I/O of EPIA-P720 Board with P720-A



Accessories



P720-A
VGA/GigaLAN/2 USB 2.0




VNT9271 Wireless USB Module
802.11b/g/n standards

Ordering Information

Model Name	CPU Frequency	Description
EPIA-P720-10EL	1.0GHz Eden™ ULV	Pico-ITX Board with 1.0GHz Eden™ ULV CPU, MPEG-2, WMV9, H.264, 1 x LVDS, 1 x HDMI, 6 x USB, 1 x IDE, 1 x SATA, 1 x GigaLAN, on-board DC-in

Block Diagram



Packing List

Items
1 x EPIA-P720-A I/O card (Pre-assembled)
1 x DC power cable
1 x SATA cable
1 x SATA power cable