



ENCLOSURE FOR 22MM PROGRAM METAL VERSION 4
COMMAND POSITIONS GRAY TOP PART

Figure similar

Enclosure:	
Design of the housing	Empty enclosure for command and signaling devices
Shape of the enclosure front	rectangular
Material of the enclosure	metal
Number of control points	4
Product component	
• protective collar	No
Color	
• of top part of the enclosure	grey
Delivery state	
• as a kit	No
• pre-wired on strip terminal	No
Mounting type of the enclosure	Vertical / horizontal
Actuator:	
Product feature	
• lockout	No
Product expansion optional Light source	Yes
Front ring:	
Product component front ring	No
General technical data:	
Product function	
• positive opening	No
• EMERGENCY STOP function	No
Product component	

• Light source	No
• Stand/pedestal	No
Vibration resistance	
• acc. to IEC 60068-2-6	20 ... 200 Hz: 5g
Protection class IP	IP67
Equipment marking	
• acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750	S
• acc. to DIN EN 61346-2	U
• acc. to DIN EN 81346-2	U

Connections/ Terminals:

Type of electrical connection on enclosure	Cable routing above, below / left, right, each 1 x M25
---	--

Ambient conditions:

Ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +80 °C

Installation/ mounting/ dimensions:

Mounting type	
• of contact blocks, socket, and accessories	Floor mounting / front mounting (1-pole)
Height	194 mm
Width	85 mm
Depth	65 mm
Shape of the installation opening	round
Mounting diameter	22 mm

Accessories:

Number of labels	4
Product component holder for 3 switching elements	No

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
--------------------------	---------------------------	-------------------	-------------------



[Special Test Certificate](#)



other

[Environmental Confirmations](#)

[Confirmation](#)

Further information



Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/industrymall>

Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB38042AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3SB38042AA3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB38042AA3&lang=en



3SB3804-2AA3_ALL

last modified:

28.04.2015