

High Current Connectors - HV M10/2 - 3049563

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




High Current Connectors, Connection method: Bolt connection, Cross section: 6 mm² - 120 mm², AWG: 10 - 250 kcmil, Width: 32 mm, Height: 73.5 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Why buy this product

- ✓ Two different partition plates can be used for the range of single and double-bolt terminal blocks
- ✓ Comprehensive range of accessories for safe and user-friendly wiring of conductors up to 120 mm²
- ✓ 2 and 3-pos. connection rails can be used for potential distribution
- ✓ Spring washers are used to prevent hexagonal nuts from loosening
- ✓ Secure connection of up to 4 conductors with cable lugs according to DIN 46234, 46235, and 46237 in a small amount of space
- ✓ The feed-through window provided in the partition plates can be easily removed for mounting the connection rails



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 310314
Weight per Piece (excluding packing)	223.03 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I

High Current Connectors - HV M10/2 - 3049563

Technical data

General

Connection in acc. with standard	IEC 60947-7-1
Current	269 A
Nominal current I_N	269 A
Nominal voltage U_N	1000 V
Open side panel	nein
Surge voltage test setpoint	9.8 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	2.2 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Tight fit on carrier	NS 35
Setpoint	15 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	120 mm ²
Short-time current	14.4 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	10 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 1, class B, body mounted
Test frequency	$f_1 = 5$ Hz to $f_2 = 150$ Hz
ASD level	0.02 g ² /Hz
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Oscillation, broadband noise test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	5 g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Shock test result	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	120 °C

Dimensions

Length	67 mm
--------	-------

High Current Connectors - HV M10/2 - 3049563

Technical data

Dimensions

Width	32 mm
Height	73.5 mm
Height NS 35/7,5	76 mm
Height NS 35/15	83.5 mm

Connection data

Conductor cross section solid min.	6 mm ²
Conductor cross section solid max.	120 mm ²
Conductor cross section stranded min.	6 mm ²
Conductor cross section stranded max.	120 mm ²
Conductor cross section AWG/kcmil min.	10
Conductor cross section AWG/kcmil max	250 kcmil
Screw thread	M10
Tightening torque, min	10 Nm
Tightening torque max	20 Nm
Connection method	Bolt connection
Connection in acc. with standard	DIN 46 234
Min. cross section	6 mm ²
Max. cross section	120 mm ²
Bolt diameter	10 mm
Tightening torque, min	10 Nm
Tightening torque max	20 Nm
Connection in acc. with standard	DIN 46,235
Min. cross section	10 mm ²
Max. cross section	95 mm ²
Bolt diameter	10 mm
Tightening torque, min	10 Nm
Tightening torque max	20 Nm

Classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 2.0	EC000897
----------	----------

High Current Connectors - HV M10/2 - 3049563

Classifications

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

CSA / CSAus / EAC / cCSAus

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	00
Nominal current I _N	225 A
Nominal voltage U _N	1000 V

CSAus	
mm ² /AWG/kcmil	00
Nominal current I _N	225 A
Nominal voltage U _N	1000 V

EAC	
-----	--

High Current Connectors - HV M10/2 - 3049563

Approvals

cCSAus

Accessories

Accessories

Bridge

Connection element - HV M10/1-VS 2 - 3049466



Connection element, Number of positions: 2, Color: silver

Connection element - HV M10/1-VS 3 - 3049479



Connection element, Number of positions: 3, Color: silver

Mounting rail

DIN rail perforated - NS 35/ 7,5 PERF 2000MM - 0801733



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2000 mm

DIN rail, unperforated - NS 35/ 7,5 UNPERF 2000MM - 0801681



DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m

High Current Connectors - HV M10/2 - 3049563

Accessories

DIN rail perforated - NS 35/ 7,5 WH PERF 2000MM - 1204119



DIN rail 35 mm (NS 35)

DIN rail - NS 35/ 7,5 WH UNPERF 2000MM - 1204122



DIN rail 35 mm (NS 35)

DIN rail, unperforated - NS 35/ 7,5 AL UNPERF 2000MM - 0801704



DIN rail, unperforated, Width: 35 mm, Height: 7.5 mm, Length: 2000 mm, Color: silver

DIN rail perforated - NS 35/ 7,5 ZN PERF 2000MM - 1206421



DIN rail, material: Galvanized, perforated, height 7.5 mm, width 35 mm, length: 2 m

DIN rail, unperforated - NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



DIN rail, material: Galvanized, unperforated, height 7.5 mm, width 35 mm, length: 2 m

High Current Connectors - HV M10/2 - 3049563

Accessories

DIN rail, unperforated - NS 35/ 7,5 CU UNPERF 2000MM - 0801762



DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m

End cap - NS 35/ 7,5 CAP - 1206560



DIN rail end piece, for DIN rail NS 35/7.5

Drawings

Circuit diagram

