

## Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Ethernet switch, 8 TP RJ45 ports, automatic detection of data transmission speed of 10/100 Mbps (RJ45), autocrossing function

### Your advantages

- ✓ Auto negotiation and autocrossing detection simplifies installation and setup
- ✓ Local diagnostic indicators with LEDs
- ✓ The switch also offers cable locking and port blocking
- ✓ QoS-prioritized (Quality of Service) messages
- ✓ DC and AC power supplies
- ✓ RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 4 6 3 5 6 4 5 7 1 4 9
GTIN	4046356457149
Weight per Piece (excluding packing)	489.400 g
Custom tariff number	85176200
Country of origin	Taiwan

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	50 mm
Height	120 mm
Depth	70 mm

#### Ambient conditions

# Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

## Technical data

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)

### Interfaces

Interface	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Note on the connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps

### Function

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
Additional functions	Autonegotiation
Status and diagnostic indicators	LEDs: U <sub>S</sub> , link and activity per port

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

### Supply voltage

Supply voltage	24 V AC/DC
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	20 V AC ... 28 V AC
	12 V DC ... 32 V DC
Typical current consumption	189 mA (at U <sub>S</sub> = 24 V AC)

### General

Mounting type	DIN rail
Type AX	Block design
Net weight	489.4 g
Housing material	Aluminum

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

# Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

## Technical data

### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	19170402
eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	19030117
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734
ETIM 7.0	EC000734

### UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

# Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

## Approvals

Ex Approvals

UL Listed / cUL Listed / cULus Listed

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
EAC			EAC-Zulassung
EAC			RU *- DE.A*30.B.01735
cULus Listed			

## Accessories

### Accessories

#### End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

#### Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250

Patch cable, CAT5, assembled, 0.3 m

## Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

### Accessories

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Patch cable, CAT5, assembled, 0.5 m

---

Patch cable - FL CAT5 PATCH 1,0 - 2832276

Patch cable, CAT5, assembled, 1 m

---

Patch cable - FL CAT5 PATCH 1,5 - 2832221

Patch cable, CAT5, assembled, 1.5 m

---

Patch cable - FL CAT5 PATCH 2,0 - 2832289

Patch cable, CAT5, assembled, 2 m

---

Patch cable - FL CAT5 PATCH 3,0 - 2832292

Patch cable, CAT5, assembled, 3 m

---

Patch cable - FL CAT5 PATCH 5,0 - 2832580

Patch cable, CAT5, assembled, 5 m

---

Patch cable - FL CAT5 PATCH 7,5 - 2832616

Patch cable, CAT5, assembled, 7.5 m

---

Patch cable - FL CAT5 PATCH 10,0 - 2832629

Patch cable, CAT5, assembled, 10 m

---

Protective cap

# Industrial Ethernet Switch - FL SWITCH SFN 8TX-24VAC - 2891020

## Accessories

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

---

## Safety locking

Port Guard Security Element - FL SEC PAC 4TX - 2832865



Layer1 security elements for four RJ45 network connections for use with patch boxes and panels