

# 12 Mini Stripping Tool



12 80 100 SB

- ▶ for stripping thin copper conductors of 0.25 - 0.8 mm dia.
- ▶ precise stripping because of the tool's stepwise adjustment to the conductor's diameter
- ▶ with wire cutter
- ▶ adjustable length stop from 4.0 - 15.0 mm

- ▶ with locking device
- ▶ shock-resistant plastic body


Article-No.	EAN-Code	Stripping capacities		△
Length mm	4003773- Code	∅ mm	AWG	g
12 80 100 SB	043119	0.25 - 0.8	30 - 20	50

# 12 Wire Stripper for Fibre Optics



12 82 130 SB

- ▶ to remove primary and secondary coating of fibre optics



Article-No.	EAN-Code	Head	Handles	Stripping capacities	△
Length mm	4003773- Code			∅ mm	g
12 82 130 SB	050094	burnished	with plastic handles	primary coating 0.125, secondary coating 0.25	55

KEVLAR® is a registered Trademark of E. I. du Pont de Nemours and Company

# 12 Stripping Tool for Fibre Optics



12 85 100 SB

- ▶ to remove primary coating of fibre optics 0.125 mm dia.
- ▶ blade dia. 0.18 mm, hole for cable feeding 0.30 mm dia.
- ▶ adjustable length stop
- ▶ shock-resistant plastic body



Removes precisely the primary coating from fibre optics

Article-No.	EAN-Code	Stripping capacities	△
Length mm	4003773- Code	∅ mm	g
12 85 100 SB	043126	to remove primary coating of fibre optics 0.125 mm dia.	40