

# WLAN outdoor camera & app

Art. no. TVAC19100B

Page 1 of 2



- For flexible outdoor use
- Guided step-by-step installation via app (iOS, Android)
- App access of up to 8 cameras
- HD 720p resolution and infrared night vision function for brilliant image quality
- Professional integrated motion detection (PIR sensor)
- E-mail notification, snapshot function and push notification via app when motion is detected
- Sturdy, weatherproof outdoor camera (IP66)
- Recording to SD card (accessory, max. 32 GB)
- Low network load thanks to compressed data transfer (H.264 compression)

## Perfect all-around protection in outdoor areas

This weatherproof WLAN outdoor camera comes with a compatible app for iOS or Android which even technical laymen can use to quickly and easily install the system. With a resolution of 720 p and integrated infrared night vision function, the camera delivers brilliant image quality both day and night.

## Event notification and mobile access via app

Movements within the detection range of the camera are reliably identified by the passive infrared sensor. Recording on the SD card starts automatically. If desired, you will be informed of incidents by e-mail or push notification and can take a snapshot or view the corresponding video image data using the app. With the app, you have simultaneous access to the image material of up to eight cameras. The efficient H.264 data compression reduces the network load to a minimum and increases the storage volume.

# WLAN outdoor camera & app

Art. no. TVAC19100B

Page 2 of 2

## Technical Data:

Dimensions	134 x 67 x 48 mm
Number of users	3 simultaneous access sessions
Image sensor	MP CMOS
Frame rate	VGA @ 20 fps / VGA @ 25 fps / 720p @ 5 fps / 720p @ 10 fps
Width	67 mm
Focal length	2,8 mm
Housing material	Waterproof metal
Height	48 mm
IR LEDs	6 IR Power LEDs
Length	134 mm
Max. operating temperature	50 °C
Min. operating temperature	-10 °C

Minimum illumination (color)	1 - 8 Lux
Net weight	0.3 kg
Network access	Ethernet (10/100 Base-T/Base-TX); Wi-Fi (IEEE 802.11 b/g/n)
Lens	TCP/IP, UDP, SMTP, NTP, DHCP, ARP
PIR range	3 m
IP protection class	66
DC voltage supply	5 V
Power consumption	1500 mA
Encryption	WPA /WPA2/WPA2-PSK (TKIP, 128 bit AES)
Video compression	H.264