



SPECIFICATION SHEET

Talento 111 / 171 & 211 / 271

PRODUCT/ORDER CODE

Talento 111 / 171 (V86/1 STu / SWu) single channel 16 Amps
 Talento 211 / 271 (V86/1 QRTu / QRWu) single channel 16 Amps

General information:

This product is suitable for din-rail mounting.
 Talento 211 is a 24 hour dial timer, with 48 x 30 minute tappets
 Talento 271 is a 7 day dial timer, with 56 x 3 hour tappets

Talento 1.. series products are synchronous units without running reserve.
 Talento 2.. series products are quartz regulated time switch devices, with a built-in battery reserve, which will maintain accurate time in the event of mains disconnection / failure.

Technical specification:

Dimensions 85 x 52.5 x 60 (3-modules)

Weight 160g

AC switching capacity:

- resistive load 16A 250v AC

- inductive load cos Ø 0.6 4A 250v AC

- incandescent lamp load 1000W

Contact type volt-free changeover

Ambient temperature -20°C to +55°C

Accuracy +/- 2.5 seconds per day @ 20°C

Running reserve (quartz only) 150 hours

Minimum switching time 24 hour – 30 minutes

7 day – 3 hours

Manual override Fix on / Fix off

