


Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 6 m



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 893071
Weight per Piece (excluding packing)	638.5 g
Custom tariff number	85444290
Country of origin	Hungary

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Length of cable	6 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	9 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Number of positions	15
---------------------	----

Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

Technical data

Connector, module side

Connectors	D-SUB socket strip
Number of plugs	1

Connector, controller side

Number of positions	15
Connectors	D-SUB pin strip
Number of plugs	1

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27249205

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized


Ex Approvals


Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

Approvals

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

CSA 

EAC

cULus Recognized 