

## KYBKM-107HMTU - Stainless steel full keyboard with Trackball - Hole mount



### Dimension:

- Front Panel: 478×135mm
- Overall: 502×159mm
- Trackball diameter: 38mm

### Applications:

- Check-in Kiosk, Info-Kiosk, Internet Kiosk, Medical Kiosk, Industrial Control Platform..

### Features:

- 104 keys stainless steel panel mount keyboard
- High quality medium travel keys
- Support OS: Windows XP/Vista/7/8 and above, Linux and Unix
- Resistant to dirt, dust and liquid
- Very rugged vandal proof design
- Can be cleaned with soapy water, disinfectant or other cleaning agents
- PS/2 or USB interface available
- Mounting kit and Desktop kit optional
- Customized layout available

### Material:

- Front Panel: 304 stainless steel
- Keys: 304 stainless steel
- Trackball: 304 stainless steel
- Back panel: Aluminum

### Mechanical Performance:

- Operating Temperature: -10°to+50°
- Storage Temperature: -30°to +80°
- Relative humidity: 30%~95%
- Atmospheric pressure: 50 to 110kPa
- Lifespan: >1 million operations per key
- Key trip: 2mm
- Key pressure: 120g
- Weight: 2.3kg

**Electrical Performance:**

- Voltage: 5.0VDC±5%
- Electric current: 10mA
- EMC Emission: EN55022(B)
- Trackball resolution: X:>200dpi Y: >190dpi

**Reliability:**

- MTBF: >20,000 hours
- MTTR: < 30 minutes

**Approvals:**

- CE, FCC, RoHS
- IP65, IK07