

# Unfortunately, stainless steel does get damaged by rust – just not in the way how you imagine!

Stainless steel looks good, and its natural properties do keep rust at bay. However, if screwdriving jobs on stainless steel fixings or fasteners are carried out with conventional carbon steel tools, steel particles from these tools remain as residues in the screw head and rust when exposed to oxygen. This is known as extraneous rust.

This ruins the positive aesthetic properties of stainless steel.

Stainless steel is a material that is currently very much in fashion, and is likely to stay that way, due to its eye-catching and modern appearance.



Solution to the rust problem: screw stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of **stainless steel** so unsightly rust can be avoided.

The stainless steel tools from Wera are vacuum ice-hardened and have the **hardness** and **strength** needed for screw connections. There are no limitations to the industrial applications they are suitable for.



Wera stainless steel tools can be easily recognised by their ice-blue design elements. This excludes the danger of them being mistaken for any other tools.

Wera screwdrivers manufactured from stainless steel have all the product advantages from the Kraftform Plus series: **Kraftform design multi-component handle, Lasertip, handle identification, non-roll feature.**





- **Stainless steel tools prevent complaints caused by rusting stainless steel!**
- **Stainless steel tools prevent high consequential costs caused by rusting stainless steel!**




Stainless steel bits are available **individually** and **in Bit-Check sets**. Bit-Checks combine a wide range of functions in a compact form. Naturally, the bits are created for professional applications i.e. no compromises in terms of service life when compared with conventional bits made from alloyed tool steel.



The stainless steel Rapidaptor bit holder allows simple handling even in the stainless steel tool line:

- **rapid bit change** with just one hand and without any additional tools
- free-rotating sleeve for stabilising the power tool
- secure clamping of long bits.



Stainless steel L-keys in Hex-Plus design **prevent rounded screw heads** and transfer up to 20% more torque.

# Stainless Steel Tools

## Keep rust at bay

### 3335 Screwdriver for slotted screws, stainless



**Application:** Slotted screws  
**Blade:** Round  
**Design:** Stainless steel, Lasertip  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05032001001 <sup>1)</sup>	0,5	3,0	3,0	80	81	1/8"	3 1/8"	10
05032002001	0,6	3,5	3,5	100	81	9/64"	4"	10
05032003001	0,8	4,0	4,0	100	98	5/32"	4"	10
05032004001	1,0	5,5	5,5	125	98	7/32"	5"	10

1) without Lasertip

### 3334 Screwdriver for slotted screws, stainless



**Application:** Slotted screws  
**Blade:** Round  
**Design:** Stainless steel, Lasertip  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05032005001	1,2	6,5	6,0	150	105	1/4"	6"	10
05032006001	1,2	8,0	7,0	175	112	5/16"	7"	10
05032007001	1,6	10,0	9,0	200	112	3/8"	8"	5

### 3350 PH Screwdriver for Phillips screws, stainless



**Application:** Phillips screws  
**Blade:** Round  
**Design:** Stainless steel, Lasertip  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm
05032020001 <sup>1)</sup>	PH 0	60	81	3,0	2 3/8"
05032021001	PH 1	80	98	4,5	3 1/8"
05032022001	PH 2	100	105	6,0	4"
05032023001	PH 3	150	112	8,0	6"

1) without Lasertip

### 3355 PZ Screwdriver for Pozidriv screws, stainless



**Application:** Suitable for Pozidriv<sup>®</sup> screws  
**Blade:** Round  
**Design:** Stainless steel, Lasertip  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm
05032030001 <sup>1)</sup>	PZ 0	60	81	3,0	2 3/8"
05032031001	PZ 1	80	98	4,5	3 1/8"
05032032001	PZ 2	100	105	6,0	4"
05032033001	PZ 3	150	112	8,0	6"

1) without Lasertip

<sup>\*)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.

### 3367 Screwdriver for TORX® screws, stainless



**Application:** TORX<sup>®</sup> socket screws  
**Blade:** Round  
**Design:** Stainless steel  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm
05032050001	TX 8	60	81	3,5	2 3/8"
05032051001	TX 9	60	81	4,0	2 3/8"
05032052001	TX 10	80	81	4,0	3 1/8"
05032053001	TX 15	80	98	4,0	3 1/8"
05032054001	TX 20	100	98	4,5	4"
05032055001	TX 25	100	105	5,0	4"
05032056001	TX 27	115	105	5,5	4 9/16"
05032057001	TX 30	115	105	6,0	4 9/16"
05032058001	TX 40	130	112	7,0	5 3/16"



## How to prevent rust when working with stainless steel




Stainless steel has the property of not rusting. However, if tools made out of conventional steel are used for stainless steel components or screws, the particles left behind from these tools can adhere to the surface and then rust. This effect – known as extraneous rust – can impair the visual appearance and even cause structural damage that may result in expensive repair work.

The wear particles that cause this rust effect can be prevented by using stainless steel tools.



## Can stainless steel tools only be used for stainless steel screws?



Stainless steel tools can, of course, be used with conventional screws. This is in no way a compromise. However, a usage that alternates between stainless steel screws and conventional screws should be avoided

to prevent any transfer of extraneous rust particles. Wera's stainless steel tools are also an excellent choice for applications in moist environments – such as for work outside, or around boats.


## 3334/6 Screwdriver set, stainless and Rack



**Application:** Slotted and Phillips screws  
**Content:** 6-piece set and Rack in display carton

Code	Icon	Part Number	Description	Quantity
05032060001	●	3334	1 x 1,2x6,5x150	1
	●	3335	1 x 0,5x3,0x80 <sup>1)</sup> ; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕	3350 PH	1 x PH 1x80; 1 x PH 2x100	

1) without Lasertip



# Stainless Steel Tools

## Keep rust at bay

### 3334/3355/6 Screwdriver set, stainless and Rack



### 3334/3350/3355/6 Screwdriver set, stainless and Rack



**Application:** Slotted and Pozidriv<sup>®</sup> screws

**Content:** 6-piece set and Rack in display carton

Code	Icons	Code	Specifications	Quantity
05032061001	●	3334	1 x 1,2x6,5x150	1
	●	3335	1 x 0,5x3,0x80 <sup>1)</sup> ; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕	3355 PZ	1 x PZ 1x80; 1 x PZ 2x100	

1) without Lasertip

<sup>\*)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.

**Application:** Slotted, Phillips and Pozidriv<sup>®</sup> screws

**Content:** 6-piece set and Rack in display carton

Code	Icons	Code	Specifications	Quantity
05032063001	●	3334	1 x 1,2x6,5x150	1
	●	3335	1 x 0,5x3,0x80 <sup>1)</sup>	
	⊕	3350 PH	1 x PH 1x80; 1 x PH 2x100	
	⊕	3355 PZ	1 x PZ 1x80; 1 x PZ 2x100	

1) without Lasertip

<sup>\*)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.



## Why have there been so few stainless steel tools until now?



Wera recently introduced a special process to finally ensure that stainless steel tools satisfy the same hardness specifications as conventional tools.

The vacuum ice-hardening process gives the tools the necessary degree of hardness needed in industrial applications. The result: tough tools made from stainless steel for stainless steel applications.

### 3367/3355/6 Screwdriver set, stainless and Rack



**Application:** TORX<sup>®</sup> and Pozidriv<sup>®</sup> screws

**Content:** 6-piece set and Rack in display carton

Code	Icons	Code	Specifications	Quantity
05032062001	⊕	3355 PZ	1 x PZ 1x80; 1 x PZ 2x100	1
	⊕	3367 TORX <sup>®</sup>	1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100	

<sup>\*)</sup> Pozidriv = reg. trademark of European Industrial Service Ltd.

### 3160 i VDE Screwdriver for slotted screws, stainless



- Application:** Slotted screws  
**Blade:** Insulated, individually tested as per IEC 60900 : 2004  
**Design:** Conical edge, Lasertip, stainless steel for minimising rust  
**Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm			
05022729001 1)	0,5	3,0	80	81	1/8"	3 1/8"	10
05022730001	0,6	3,5	100	81	9/64"	4"	10
05022731001	0,8	4,0	100	98	5/32"	4"	10
05022732001	1,0	5,5	125	98	7/32"	5"	10

1) without Lasertip

### 3162 i VDE PH Screwdriver for Phillips screws, stainless



- Application:** Phillips screws  
**Blade:** Insulated, individually tested as per IEC 60900 : 2004  
**Design:** Lasertip, stainless steel for minimising rust  
**Handle:** Kraftform with non-roll feature, multi-component

Code		mm	mm		
05022733001	PH 1	80	98	3 1/8"	10
05022734001	PH 2	100	105	4"	10

### 3160 i/7 Screwdriver set, stainless and Rack



Kraftform stainless: the safety screwdriver for stainless steel screws, Lasertip blade + voltage tester + Rack

- Application:** Slotted and Phillips screws  
**Contents:** Stainless steel, 7-piece set and Rack in display carton

Code				
05022728001	⊖	3160 i VDE	1 x 0,5x3,0x80 1); 1 x 0,6x3,5x100; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	1
	⊕	3162 i VDE	1 x PH 1x80; 1 x PH 2x100	
	⊖	3247	1 x 0,5x3,0x70	

1) without Lasertip

# Stainless Steel Tools

## Keep rust at bay

### 3950 PKL L-key, metric, stainless



**Hex-Plus**



**Application:** Hexagon socket screws

**Design:** Stainless steel

**Tip:** Hex-Plus, ball-end hexagon on long arm

Code	mm	mm	mm	mm	mm	
05022700001	1,5	90	14	3 1/2"	9/16"	10
05022701001	2,0	101	16	4"	5/8"	10
05022702001	2,5	112	19	4 7/16"	3/4"	10
05022703001	3,0	123	21	4 7/8"	27/32"	10
05022704001	4,0	137	24	5 3/8"	1"	10
05022705001	5,0	154	27	6 1/16"	1 1/16"	10
05022706001	6,0	172	31	6 3/4"	1 1/4"	10
05022708001	8,0	195	37	7 11/16"	1 7/16"	10
05022709001	10,0	224	42	9"	1 11/16"	10

### 3950 PKL L-key, imperial, stainless



**Hex-Plus**



**Application:** Hexagon socket screws

**Design:** Stainless steel

**Tip:** Hex-Plus, ball-end hexagon on long arm

Code	mm	mm	mm	mm	mm	
05022710001	3/32"	112	19	4 7/16"	3/4"	10
05022711001	7/64"	119	20	4 3/4"	25/32"	10
05022712001	1/8"	123	21	4 7/8"	27/32"	10
05022713001	9/64"	130	22	5 3/16"	29/32"	10
05022714001	5/32"	137	24	5 3/8"	1"	10
05022715001	3/16"	154	27	6 1/16"	1 1/16"	10
05022716001	1/4"	185	34	7 1/4"	1 5/16"	10
05022717001	5/16"	195	37	7 11/16"	1 7/16"	10
05022718001	3/8"	224	42	9"	1 11/16"	5

### 3950 PKL/9 L-key set, metric, stainless



**Hex-Plus**



9-piece set in a two-component clip

Code			
05022720001	3950 PKL	1 x 1,5x90; 1 x 2,0x101; 1 x 2,5x112; 1 x 3,0x123; 1 x 4,0x137; 1 x 5,0x154; 1 x 6,0x172; 1 x 8,0x195; 1 x 10,0x224	10

### 3950 PKL/9 SZ L-key set, imperial, stainless



**Hex-Plus**



9-piece set in belt pouch

Code			
05022721001	3950 PKL inch	1 x 3/32"x112; 1 x 7/64"x119; 1 x 1/8"x123; 1 x 9/64"x130; 1 x 5/32"x137; 1 x 3/16"x154; 1 x 1/4"x185; 1 x 5/16"x195; 1 x 3/8"x224	1



**Hex-Plus**

**How can I avoid rounding the head of the socket?**



Hexagon socket screws can be problematic because of the very narrow contact surfaces that transfer torque from the tool to the screw. This can destroy the head of the screw. Hex-Plus tools provide a greater contact surface to prevent this and fit every standard hexagon socket screw.

### Kraftform Kompakt 60, stainless



Hex-Plus



Belt pouch with 89 mm bits, stainless steel

17-piece set

1 stainless hand-held bit holder 3816 R with Rapidaptor quick-release chuck

Code	Icon	Code	Description	Quantity
05071116001	●	3816 R	1 x 1/4"x119	1
	●	3800/4	1 x 1,0x5,5x89	
	○	3840/4	1 x 3,0x89; 1 x 4,0x89; 1 x 5,0x89;	
		Hex-Plus	1 x 6,0x89	
	⊕	3851/4	1 x PH 1x89; 1 x PH 2x89; 1 x PH 3x89	
	⊕	3855/4	1 x PZ 1x89; 1 x PZ 2x89; 1 x PZ 3x89	
	⊕	3867/4	1 x TX 10x89; 1 x TX 15x89; 1 x TX 20x89;	
		TORX® B0	1 x TX 25x89; 1 x TX 30x89	

### 3816 R Bit-holding screwdriver with Rapidaptor quick-release chuck, stainless



**Application:** Suitable for 1/4" hexagon insert bits, DIN 3126-C 6.3 and E 6.3 (ISO 1173) and Wera Series 1 and 4

**Drive:** 1/4" hexagon with Rapidaptor rapid-in, rapid-out, rapid-spin, chuck-all and single-hand technology

**Handle:** Kraftform with non-roll feature, multi-component

Code	Icon	Icon	mm	Quantity
05051465001	●	●	1/4" 119	5

### Kraftform Kompakt 60, imperial, stainless



Hex-Plus



Belt pouch with 89 mm bits, stainless steel

17-piece set

1 stainless hand-held bit holder 3816 R with Rapidaptor quick-release chuck

Code	Icon	Code	Description	Quantity
05071117001	●	3816 R	1 x 1/4"x119	1
	●	3800/4	1 x 1,0x5,5x89	
	○	3840/4	1 x 3/32"x89; 1 x 1/8"x89; 1 x 5/32"x89;	
		Hex-Plus	1 x 3/16"x89	
	⊕	3851/4	1 x PH 1x89; 1 x PH 2x89; 1 x PH 3x89	
	⊕	3867/4 TORX®	1 x TX 10x89; 1 x TX 15x89; 1 x TX 20x89;	
		B0	1 x TX 25x89; 1 x TX 30x89	
	○	3868/4	1 x # 1; 1 x # 2; 1 x # 3	
		Square-Plus		



# Stainless Steel Tools

## Keep rust at bay

### 3851/1 TS bits, stainless



**TORSION**



**Application:** Phillips screws

**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders

**Design:** Stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	Drive	mm	Length	Quantity
05071010001	PH 1	25	1"	10
05071011001	PH 2	25	1"	10
05071012001	PH 3	25	1"	10

### 3851/4 Bits, stainless



**Application:** For Phillips screws

**Drive:** 1/4" hexagon, suitable for DIN 3126-F 6.3, ISO 1173 bit holders

**Design:** Stainless steel for minimising rust

Code	Drive	mm	Length	Quantity
05071081001	PH 1	89	3 1/2"	10
05071082001	PH 2	89	3 1/2"	10
05071083001	PH 3	89	3 1/2"	10

### 3855/1 TS bits, stainless



**TORSION**



**Application:** Suitable for Pozidriv<sup>®</sup> screws

**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders

**Design:** Stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	Drive	mm	Length	Quantity
05071020001	PZ 1	25	1"	10
05071021001	PZ 2	25	1"	10
05071022001	PZ 3	25	1"	10

\*) Pozidriv = reg. trademark of European Industrial Service Ltd.

### 3855/4 Bits, stainless



**Application:** Suitable for Pozidriv<sup>®</sup> screws

**Drive:** 1/4" hexagon, suitable for DIN 3126-F 6.3, ISO 1173 bit holders

**Design:** Stainless steel for minimising rust

Code	Drive	mm	Length	Quantity
05071084001	PZ 1	89	3 1/2"	10
05071085001	PZ 2	89	3 1/2"	10
05071086001	PZ 3	89	3 1/2"	10

\*) Pozidriv = reg. trademark of European Industrial Service Ltd.

### 3867/1 TS TORX<sup>®</sup> bits, stainless



**TORSION**



**Application:** TORX<sup>®</sup> socket screws

**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders

**Design:** Stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	Drive	mm	Length	Quantity
05071030001	TX 8	25	1"	10
05071031001	TX 9	25	1"	10
05071032001	TX 10	25	1"	10
05071033001	TX 15	25	1"	10
05071034001	TX 20	25	1"	10
05071035001	TX 25	25	1"	10
05071036001	TX 27	25	1"	10
05071037001	TX 30	25	1"	10
05071038001	TX 40	25	1"	10

### 3867/1 TZA TORX<sup>®</sup> bits with safety pin, stainless



**TORSION**



**TStar<sup>®</sup>  
for SPAX<sup>®</sup>-  
Screws**

**Application:** TORX<sup>®</sup> with bore hole

**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders

**Design:** TORX<sup>®</sup> with safety pin, stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	Drive	mm	Length	Quantity
05071050001	TX 10	25	1"	10
05071051001	TX 15	25	1"	10
05071052001	TX 20	25	1"	10
05071053001	TX 25	25	1"	10
05071054001	TX 30	25	1"	10
05071055001	TX 40	25	1"	10

### 3867/4 TORX® BO bits with bore hole, stainless



**Application:** TORX® socket screws with safety pin (BO = with bore hole)  
**Drive:** 1/4" hexagon suitable for DIN 3126-F 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust

Code	mm	mm	mm	
05071089001	TX 10 BO	89	3 1/2"	4,0
05071090001	TX 15 BO	89	3 1/2"	4,0
05071091001	TX 20 BO	89	3 1/2"	4,5
05071092001	TX 25 BO	89	3 1/2"	6,0
05071094001	TX 30 BO	89	3 1/2"	6,0

### 3800/1 TS bits for slotted screws, stainless



**Application:** Slotted screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	mm	mm	mm	mm
05071000001	0,8	5,5	25	1"
05071001001	1,0	5,5	25	1"
05071002001	1,2	6,5	25	1"


### 3800/4 Bits for slotted screws, stainless



**Application:** Slotted screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-F 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust

Code	mm	mm	mm	mm
05071080001	1,0	5,5	89	3 1/2"

### 3840/1 TS bits, stainless



**Application:** Hexagon socket screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders  
**Design:** Hex-Plus, stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	mm	mm	mm	mm
05071070001	1,5		25	1"
05071071001	2,0		25	1"
05071072001	2,5		25	1"
05071073001	3,0		25	1"
05071074001	4,0		25	1"
05071075001	5,0		25	1"
05071077001	5,5		25	1"
05071076001	6,0		25	1"
05071060001		3/32"	25	1"
05071061001		7/64"	25	1"
05071062001		1/8"	25	1"
05071063001		9/64"	25	1"
05071064001		5/32"	25	1"
05071065001		5/64"	25	1"
05071066001		1/4"	25	1"

### 3840/4 Bits, stainless



**Application:** Hexagon socket screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-F 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust

Code	mm	mm	mm	mm
05071101001	3,0	89	3 1/2"	10
05071102001	4,0	89	3 1/2"	10
05071103001	5,0	89	3 1/2"	10
05071104001	6,0	89	3 1/2"	10
05071105001		3/32"	89	3 1/2"
05071106001		1/8"	89	3 1/2"
05071107001		5/32"	89	3 1/2"
05071108001		3/16"	89	3 1/2"

# Stainless Steel Tools

## Keep rust at bay

### 3868/1 TS Square-Plus bits, stainless



**TORSION**



**Application:** Square socket screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-D 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust, special torsion-style design to reduce premature wear

Code	#	mm	1"	
05071025001	# 2	25	1"	10

### 3868/4 Square socket bits, stainless



**Application:** Square socket screws  
**Drive:** 1/4" hexagon, suitable for DIN 3126-F 6.3, ISO 1173 bit holders  
**Design:** Stainless steel for minimising rust

Code	#	mm	3 1/2"	mm	
05071097001	# 1	89	3 1/2"	4,5	10
05071098001	# 2	89	3 1/2"	5,0	10
05071099001	# 3	89	3 1/2"	5,5	10

### 3888/4/1 K Rapidaptor universal bit holder, stainless



**Application:** Suitable for 1/4" DIN 3126-C 6.3 and E 6.3 (ISO 1173) hexagon insert bits and Wera Series 1 and 4  
**Design:** Rapidaptor rapid-in, rapid-out, rapid-spin, chuck-all and single-hand technology  
**Drive:** 1/4" hexagon, suitable for power tools with DIN 3126-F 6.3, ISO 1173 chuck

Code	1/4"	mm	2"	1/4"	mm	
05071100001	1/4"	50	2"	1/4"	15,0	5

### BC Stainless/30 Bit-Check



**Hex Plus**

**TORSION**



29 bits and 1 Rapidaptor stainless steel bit holder: stainless tools minimise the formation of rust on stainless steel screws

Code			
05071109001	● 3888/4/1 K	1 x 1/4"x50	1
	○ 3840/1 TS	1 x 2,5x25; 1 x 3,0x25; 1 x 4,0x25; 1 x 5,0x25; 1 x 5,5x25	
	⊕ 3851/1 TS PH	1 x PH 1x25; 3 x PH 2x25; 1 x PH 3x25	
	⊕ 3855/1 TS PZ	2 x PZ 1x25; 3 x PZ 2x25; 1 x PZ 3x25	
	○ 3867/1 TS TORX®	2 x TX 10x25; 2 x TX 15x25; 3 x TX 20x25; 3 x TX 25x25; 2 x TX 30x25; 1 x TX 40x25	



**How can I change bits as quickly and safely as possible?**




With the Wera Rapidaptor 1/4" bits can be inserted and automatically locked in the holder without using the slide switch. Even the smallest bits are easily removed by sliding the sleeve forward. The free-spinning outer sleeve stabilises battery or mains-powered tools during the screwdriving process. All functions can be carried out with just one hand. There is no faster bit change!

### BC 10/9 Bit-Check, stainless



**TORSION**



1 Rapidaptor bit holder 3888/4/1 K, stainless steel with quick-release chuck, suitable for power tools and electric drills

Code	Icon	Code	Quantity	Code
05071110001	⊙	3888/4/1 K	1 x 1/4"x50	10
	⊕	3851/1 TS PH	1 x PH 2x25	
	⊕	3855/1 TS PZ	1 x PZ 1x25; 2 x PZ 2x25	
	⊙	3867/1 TS	1 x TX 10x25; 1 x TX 15x25; 1 x TX 20x25; TORX®	
			1 x TX 25x25; 1 x TX 30x25	

### BC 11/9 Bit-Check, stainless



**Hex-Plus**

**TORSION**



1 Rapidaptor bit-holder 3888/4/1 K, stainless steel with quick-release chuck, suitable for power tools and electric drills

Code	Icon	Code	Quantity	Code
05071112001	⊙	3888/4/1 K	1 x 1/4"x50	10
	⊙	3840/1 TS	1 x 2,5x25; 1 x 3,0x25; 1 x 4,0x25; 1 x 5,0x25	
	⊕	3851/1 TS PH	2 x PH 1x25; 2 x PH 2x25; 1 x PH 3x25	

### Stainless steel case



1 x 3334/6; 1 x 3950 PKL/9; 1 x BC 10/9; in practical storage and transport case

Code	Icon	Code	Quantity	Code
05071118001				1

### 3869/4 Nutsetters, stainless



**Application:** Hexagon headed bolts, screws and nuts

**Drive:** 1/4" hexagon, suitable for power tools with DIN 3126-F 6.3, ISO 1173 chuck

**Design:** Non-magnetic, retaining spring, stainless steel for minimising rust

Code	mm	mm	mm	Code
05071220001	5,0	50,0	9,5	5
05071221001	5,5	50,0	9,5	5
05071222001	7,0	50,0	12,5	5
05071223001	8,0	50,0	14,0	5
05071224001	10,0	50,0	16,0	5
05071225001	13,0	50,0	19,5	5
05071226001		1/4"	50,0	5
05071227001		5/16"	50,0	5
05071228001		3/8"	50,0	5
05071229001		1/2"	50,0	5

### 3869/8 Nutsetter set, stainless



8-piece set, stainless steel, retaining spring, in practical belt pouch

Code	Icon	Code	Quantity	Code
05071230001	⊙	3869/4	1 x 5,0x50,0; 1 x 5,5x50,0; 1 x 7,0x50,0; 1 x 8,0x50,0; 1 x 10,0x50,0; 1 x 13,0x50,0; 1 x 1/4"x50,0; 1 x 3/8"x50,0	1