

Connection honeycomb - W 80/ 80-FS/FS(12-2,8-0,8) - 0611017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Connection honeycomb, Connection method: Slip-on connection, Mounting type: Direct screw connection, Number of positions: 80, Color: green

Key commercial data

Packing unit	5 pc
GTIN	 4 017918 003104
Weight per Piece (excluding packing)	541.98 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

General

Number of levels	1
Number of connections	960
Color	green
Insulating material	PA/F
Inflammability class according to UL 94	HB
Maximum load current	16 A
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC / EN
Nominal current I_N	16 A (current data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross section.)
Nominal voltage U_N	1000 V (voltage data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross section.)
Number of positions	80

Dimensions

Width	146 mm
-------	--------

Connection honeycomb - W 80/ 80-FS/FS(12-2,8-0,8) - 0611017

Technical data

Dimensions

Length	164 mm
Height	38 mm

Connection data

Slip-on connection	6.3/2.8 x 0.8 mm
--------------------	------------------

Classifications

eCl@ss

eCl@ss 4.0	27141124
eCl@ss 4.1	27141124
eCl@ss 5.0	27141124
eCl@ss 5.1	27141124
eCl@ss 6.0	27141124
eCl@ss 7.0	27141124
eCl@ss 8.0	27141124

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Connection honeycomb - W 80/ 80-FS/FS(12-2,8-0,8) - 0611017

Approvals

Approval details

GOST 

Accessories

Accessories

Equipotential bonding strip

Equipotential busbar - S-FS (2,8X0,8) - 3191699



Potential busbar, with slotted 6.3/2.8 mm flat connectors, max. 40 A, brass, tin-plated, length: 1 m