

# Specifications for BMP71 Label Printer Tapes

|                                  |  |
|----------------------------------|--|
| <b>Adhesive</b>                  | Permanent Acrylic  |
| <b>Application</b>               | General & Industrial Identification; Pipe Marking  |
| <b>Article No.</b>               | 142344   |
| <b>Brady Material No.</b>        | <a href="#">B-595</a>  |
| <b>Material Type</b>             | Vinyl  |
| <b>Colour</b>                    | Clear  |
| <b>Finish</b>                    | Gloss  |
| <b>Laboratory Application</b>    | Well Plates;General Identification   |
| <b>Description</b>               | B-595 vinyl will adhere to difficult low surface energy items, including: PVC piping, blow-molded equipment cases, ABS plastics, powder-coated surfaces and equipment made from recycled plastics. The B-595 material also excels at sticking to highly textured surfaces such as painted cinder block walls, finished uneven wood, textured plastics, rough-pipes and paper-jacketed pipes. |
| <b>Max. Service Temp. °C</b>     | 82   |
| <b>Order Reference</b>           | M71C-1000-595-CL   |
| <b>Printer Compatibility</b>     | BMP71  |
| <b>Ribbon Series</b>             | M71-R6000HF  |
| <b>Shape</b>                     | Continuous   |
| <b>Size - Length (m)</b>         | 15.24  |
| <b>Size - Width (mm)</b>         | 25.40  |
| <b>Total Qty per Pack</b>        | 1 Roll(s) / Box  |
| <b>Industry</b>                  | Facility & Safety Identification;General Industry;Manufacturing;Process  |
| <b>Min. Application Temp. °C</b> | -18  |
| <b>Min. Service Temp. °C</b>     | -40  |
| <b>QTY. per Row</b>              | 1  |
| <b>Thickness (mm)</b>            | 0.1  |