


# HBL5256




Nickel plated brass flange, brown phenolic (mounting screws packed separately).

## Product Specifications

<b>Device Type</b>	Flanged Receptacle
<b>Standard</b>	NEMA
<b>Amperage</b>	15A
<b>Voltage</b>	125V
<b>Poles and Wires</b>	2 Pole, 3 Wire Grounding
<b>Wiring Method</b>	Side Wire Only
<b>Hospital Grade ?</b>	No
<b>Receptacle Grade</b>	Heavy Duty Spec Grade
<b>Face Style</b>	Finder Groove
<b>Flange Style</b>	Standard Metallic
<b>Color</b>	 Brown
<b>NEMA No.</b>	5-15R
<b>Horsepower</b>	0.5
<b>Description</b>	Heavy Duty Straight Blade Flanged Receptacle
<b>Type</b>	2 Pole, 3 Wire, Grounding
<b>Rating</b>	15A, 125V
<b>Certification</b>	UL Listed, File E2186, Meets NEMA WD-6 requirements Listed to UL Standard 498, Certified to CSA, C22.2, No. 42
<b>Terminal Screw Material</b>	#8-32 Brass, Multiple Drive
<b>Ground Screw Material</b>	#8-32 Brass, Multiple Drive (Green)
<b>Top Material</b>	Phenolic
<b>Base Material</b>	Phenolic
<b>Power Contacts Material</b>	.031" (.8) Phosphor Bronze
<b>Mounting Screw Material</b>	Brass-Nickel Plated
<b>Dielectric Voltage</b>	Withstands 2,000V minimum.
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
<b>Terminal</b>	Terminals identified in accordance with UL498 (Brass, White, Green).

<b>Identification</b>	
<b>Terminal Accommodation</b>	#14-#10 AWG copper stranded or solid conductor only.
<b>Product Identification</b>	Ratings are a permanent part of the device.
<b>Flammability</b>	UL 94 V2.
<b>Operating Temperatures</b>	Maximum continuous 75°C, minimum -40°C (w/o impact).



Hubbell Incorporated (Delaware)  
 185 Plains Road  
 Milford, CT 06460-2420  
 Ph: (203) 882-4800  
 Fax: (800) 255-1031

