



Flow monitoring
Immersion sensor without integrated processor
FCS-G1/4A4-NA-H1141



- Flow sensor for liquid media
- Calorimetric principle
- Adjustment via potentiometer on processor
- Status indicated via LED chain on signal processor
- Plug-in device, M12 x 1
- 4-wire connection to the processor

Wiring Diagram



Functional principle

Our insertion - flow sensors operate on the principle of thermodynamics. The measuring probe is heated by several °C as against the flow medium. When fluid moves along the probe, the heat generated in the probe is dissipated. The resulting temperature is measured and compared to the medium temperature. The flow status of every medium can be derived from the evaluated temperature difference. Thus TURCK's wear-free flow sensors reliably monitor the flow of gaseous and liquid media.

Type code FCS-G1/4A4-NA-H1141
Ident no. 6870304

Mounting conditions insertion style sensor
Water Operating Range 1...150cm/s
Oil Operating Range 3...300 cm/s
Stand-by time typ. 8 s (2...15 s)
Switch-on time typ. 2 s (1...15 s)
Switch-off time typ. 2 s (1...15 s)
Temperature jump, response time max. 12 s
Temperature gradient ≤ 250 K/min
Medium temperature -20...80 °C

Protection class IP67

Housing material stainless steel, V4A (1.4571)
Sensor material stainless steel, AISI 316Ti
Max. tightening torque housing nut 30 Nm
Connection flange connector, M12 x 1
Pressure resistance 100 bar
Process connection G 1/4"

Flow monitoring
Immersion sensor without integrated processor
FCS-G1/4A4-NA-H1141

Wiring accessories

Type code	Ident no.	Description	Design
RKC4.4T-2/TXL	6625503	Connection cable, female M12, straight, 4-pin, cable length: 2 m, sheath material: PUR, black; cULus approval; other cable lengths and qualities available, see www.turck.com	
WKC4.4T-2/TXL	6625515	Connection cable, female M12, angled, 4-pin, cable length: 2 m, sheath material: PUR, black; cULus approval; other cable lengths and qualities available, see www.turck.com	
RKC4.4T-2/TEL	6625013	Connection cable, female M12, straight, 4-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com	
WKC4.4T-2/TEL	6625025	Connection cable, female M12, angled, 4-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com	