

Extra-Hard Use Ground Continuity Monitoring (GCM) Connector, Black & White

PS5369XGCM



Straight Blade GCM Connector 3W 20A
125V



features & benefits

- Integral indication of ground continuity and power status. Continuous monitoring enhances personnel safety and adds convenience.
- Dual, bright LED indicators with 360 degree visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross. For 250V configurations: Hot to ground cross will be indicated by a green and red LED.
- Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.
- Exclusive two-piece cord grip accepts a wide range of cord widths. Provides more consistent pressure for superior conductor retention.
- Internal dust shield keeps terminals free of contaminants.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.
- Color-coded terminal screws are positioned on the same plane and backed-out for fast installation.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White, Black

Listing Agencies/Third Party Information

CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: No
UN SPS C: 39121402
UR: No

Dimensions

Depth U S: 2.638"
Diameter U S: 1.358"

Technical Information

Amps: 20 Amp
Volts A C: 125
Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant