

C881545

G

F

E

D

C

B

A

8

7

6

5

4

3

2

1

DO NOT SCALE

DIMENSIONS IN mm.




METRIC

3rd ANGLE PROJECTION


ATENÇÃO

Este desenho esta sob o controle das especificações nos. 102-23 e 102-55. Toda e qualquer alteração, antes de ser processada, deverá ser comunicada aos clientes envolvidos, através dos procedimentos atuais.

Ver pasta "Notificação ao Cliente"



SECÇÃO A-A



SECÇÃO B-B

V2, COLOR GREEN (AMP A6484)

10 SIMILAR DO P/N 881545-2, PORÉM EM EMBALAGENS C/ 2.000 PEÇAS/SACO PLÁSTICO.

SIMILAR OF P/N 881545-2 BUT IN PACKAGES W/ 2.000 PARTS/ PLASTIC BAG.

11 MATERIAL HOUSING: TERMOPLÁSTICO COM 15% FIBRA DE VIDRO, V2, COR AMARELO (RAL 1016) CONTATO: BRONZE FOSFOROSO

MATERIAL HOUSING: THERMOPLASTIC 15% GLASS FIBER V2, COLOR YELLOW (RAL 1016) CONTACT: PHOSPHOROUS BRONZE.

12 MATERIAL HOUSING TERMOPLÁSTICO COM 15% FIBRA DE VIDRO, V2, COR VERDE (AMP A6484) CONTATO: BRONZE FOSFOROSO MATERIAL HOUSING THERMOPLASTIC 15% GLASS FIBER, V2, COLOR GREEN (AMP A6484) CONTACT: PHOSPHOROUS BRONZE.

13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

NOTAS:

NOTES:

1 MATERIAL: HOUSING: TERMOPLÁSTICO C/ FIBRA DE VIDRO V-0 COR: PRETO CONTATO: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-0 COLOR: BLACK CONTACT: PHOSPHOROUS BRONZE

2 MATERIAL: HOUSING: TERMOPLÁSTICO C/ FIBRA DE VIDRO HB COR: NATURAL CONTATO: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER HB COLOR: NATURAL CONTACT: PHOSPHOROUS BRONZE

3 0,38 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 0,38 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

4 0,76 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 0,76 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

5 1,27 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 1,27 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

6 ESTANHO SOBRE NIQUEL TIN OVER NICKEL

7 PONTO DE CONTATO P/ MEDIÇÃO DA CAMADA DE OURO CONTACT POINT FOR GOLD PLATING MEASUREMENT



8 ACEITA PINO QUADRADO 0,64 x 0,64 OU REDONDO Ø 0,64 ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND Ø 0,64

9 MATERIAL: HOUSING: TERMOPLÁSTICO C/ 15% DE FIBRA DE VIDRO, V2, COR VERMELHO (PADRÃO DE COR: RAL 3000) CONTATO: BRONZE FOSFOROSO MATERIAL: HOUSING THERMOPLASTIC WITH 15% GLASS FIBER, V2, COLOR RED (STAND COLOR: RAL 3000) CONTACT: PHOSPHOROUS BRONZE.

6	1	4-	-2
3	2	4-	-1
13	13	3	-1
6	1	2	-4
4	1	2-	-5
13	13	2-	-2
6	1	2	-1
13	13	2	-9
6	1	10	-8
4	1		-7
3	1		-6
13	13		-5
6	1		-4
4	1		-3
3	1		-2
1	1		
		881545-1	

OTHER TREATMENT	FINISH	MATERIAL	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY		881545-1	
THIS DRAWING IS UNPUBLISHED / RELEASED FOR PUBLICATION			
TOLERANCES UNLESS OTHERWISE STATED DEC. ±0.5 ANGLES ±1°		INS. DIA. RANGE	WIRE RANGE
DR. <i>[Signature]</i> 11-09-88		SCALE	
CHK. <i>[Signature]</i> 09-11-88		DESCRIPTION	
ISS. <i>[Signature]</i> 26/12/88		AMP SHUNT	
REVISED PER ECO-11-005139		LOW PROFILE CONNECTOR ASSY	
K2	REVISION RECORD	DR	CHK
155	DATE	APP	DATE
A2		DWG NO	REV
C 881545		K2	10/2

C 881545



OBSOLETE 13	6		2	8
	6		2	7
	4		2	6
	3	2	2	881545-5
OBSOLETE 13	6		1	8
	6		1	7
	4		1	6
	3	2	1	5
13 OBSOLETE	6		1	4
	6		1	3
	4		1	2
	3	1	1	881545-1
OTHER TREATMENT		FINISH	MATERIAL	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY		THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19		
SEE SHEET 1 OF 2		TOLERANCES UNLESS OTHERWISE STATED. DEC. ±0.5 ANGLES ±1°	INS. DIA. RANGE	WIRE RANGE
		DR. <i>[Signature]</i> 11-09-88	SCALE	
		CHK. <i>[Signature]</i> 08-11-88	 TE Connectivity	
		DE. <i>[Signature]</i>	DESCRIPTION AMP SHUNT	
ISS		REVISION RECORD	DR	CHK
		DATE	APP. <i>[Signature]</i> 29/12/88	DWG NO A2
				REV. K2
				SHEET 2 OF 2
				PART NUMBER C 881545