

Printed-circuit board connector - CCDN 2,5/15-G1 P26 THR - 1734407

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Rated voltage (III/2): 400 V, Number of positions: 15, Pitch: 5 mm, Color: black, Contact surface: Tin, Mounting: Taped SMD/THT/THR components




The figure shows a 10-pos. version with 20 contacts

Why buy this product

- Can be specially combined with FKCN 2,5 compact spring-cage plug
- Plug-in direction parallel to the PCB
- Standard pin length of 2.6 mm
- Minimal space required on the PCB
- Double-level base strip without offset levels
- Use in SMT reflow processes



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 177276 |
| Weight per Piece (excluding packing) | 18.86 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|----------------|---------|
| Length | 17.6 mm |
| Pitch | 5 mm |
| Dimension a | 70 mm |
| Pin dimensions | 1 x 1 |
| Hole diameter | 1.6 mm |

General

Printed-circuit board connector - CCDN 2,5/15-G1 P26 THR - 1734407

Technical data

General

| | |
|---|--------------------|
| Range of articles | CCDN 2,5/..-G1-THR |
| Insulating material group | IIIa |
| Rated surge voltage (III/3) | 4 kV |
| Rated surge voltage (III/2) | 4 kV |
| Rated surge voltage (II/2) | 4 kV |
| Rated voltage (III/3) | 320 V |
| Rated voltage (III/2) | 400 V |
| Rated voltage (II/2) | 400 V |
| Connection in acc. with standard | EN-VDE |
| Nominal current I_N | 12 A |
| Maximum load current | 12 A |
| Insulating material | LCP |
| Inflammability class according to UL 94 | V0 |
| Color | black |
| Number of positions | 15 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

Approvals

Approvals

Printed-circuit board connector - CCDN 2,5/15-G1 P26 THR - 1734407

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

| | | |
|--------------------|-------|-------|
| UL Recognized | | |
| | B | D |
| Nominal current IN | 10 A | 10 A |
| Nominal voltage UN | 300 V | 300 V |

| | | |
|--------------------|-------|-------|
| cUL Recognized | | |
| | B | D |
| Nominal current IN | 10 A | 10 A |
| Nominal voltage UN | 300 V | 300 V |


EAC

| | | |
|------------------|--|--|
| cULus Recognized | | |
|------------------|--|--|

Drawings

Printed-circuit board connector - CCDN 2,5/15-G1 P26 THR - 1734407

Drilling diagram



Dimensioned drawing

