

Thermofit[®] Molded Parts
Specification Control Drawing

Part Number : 202D211 thru 299
Description : Boot, Straight With Lip

NOTES

- 1. All dimensions are in $\frac{\text{inches}}{\text{[millimeters]}}$
- 2. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
- 3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- 4. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.





TABLE OF DIMENSIONS

PART NUMBER	H		J			P	JO	R	S	T	U	HW	JW
	Min	Max	Min	Min	Max	±10%	±10%	Ref	Ref	Ref	±10%	±20%	±20%
	a	b	$\frac{-13}{-30}a$	$\frac{-5}{-12}a$	b	b	b	b	b	b	b	b	b
202D211	$\frac{.88}{[22,4]}$	$\frac{.45}{[11,4]}$	$\frac{.88}{[22,4]}$	$\frac{.55}{[14,0]}$	$\frac{.25}{[6,4]}$	$\frac{4.17}{[105,9]}$	$\frac{3.40}{[86,4]}$	$\frac{.46}{[11,7]}$	$\frac{.12}{[3,0]}$	$\frac{.04}{[1,0]}$	$\frac{.56}{[14,2]}$	$\frac{.06}{[1,52]}$	$\frac{.045}{[1,14]}$
202D221	$\frac{1.01}{[25,7]}$	$\frac{.59}{[15,0]}$	$\frac{1.01}{[25,7]}$	$\frac{.63}{[16,0]}$	$\frac{.29}{[7,4]}$	$\frac{4.77}{[121,2]}$	$\frac{3.88}{[98,6]}$	$\frac{.48}{[12,2]}$	$\frac{.12}{[3,0]}$	$\frac{.04}{[1,0]}$	$\frac{.59}{[15,0]}$	$\frac{.06}{[1,52]}$	$\frac{.045}{[1,14]}$
202D232	$\frac{1.16}{[29,5]}$	$\frac{.74}{[18,8]}$	$\frac{1.16}{[29,5]}$	$\frac{.72}{[18,3]}$	$\frac{.33}{[8,4]}$	$\frac{5.46}{[138,7]}$	$\frac{4.44}{[112,8]}$	$\frac{.48}{[12,2]}$	$\frac{.12}{[3,0]}$	$\frac{.04}{[1,0]}$	$\frac{.61}{[15,5]}$	$\frac{.07}{[1,78]}$	$\frac{.045}{[1,14]}$
202D242	$\frac{1.34}{[34,0]}$	$\frac{.90}{[22,9]}$	$\frac{1.34}{[34,0]}$	$\frac{.84}{[21,3]}$	$\frac{.38}{[9,7]}$	$\frac{6.28}{[159,5]}$	$\frac{5.15}{[130,8]}$	$\frac{.48}{[12,2]}$	$\frac{.12}{[3,0]}$	$\frac{.04}{[1,0]}$	$\frac{.62}{[15,7]}$	$\frac{.07}{[1,78]}$	$\frac{.045}{[1,14]}$
202D253	$\frac{1.47}{[37,3]}$	$\frac{1.16}{[29,5]}$	$\frac{1.47}{[37,3]}$	$\frac{.91}{[23,1]}$	$\frac{.41}{[10,4]}$	$\frac{7.00}{[177,8]}$	$\frac{5.60}{[142,2]}$	$\frac{.55}{[14,0]}$	$\frac{.12}{[3,0]}$	$\frac{.065}{[1,65]}$	$\frac{.71}{[18,0]}$	$\frac{.08}{[2,0]}$	$\frac{.045}{[1,14]}$
202D263	$\frac{1.72}{[43,7]}$	$\frac{1.34}{[34,0]}$	$\frac{1.72}{[43,7]}$	$\frac{1.07}{[27,2]}$	$\frac{.48}{[12,2]}$	$\frac{8.00}{[203,2]}$	$\frac{6.42}{[163,1]}$	$\frac{.60}{[15,2]}$	$\frac{.12}{[3,0]}$	$\frac{.065}{[1,65]}$	$\frac{.78}{[19,8]}$	$\frac{.08}{[2,0]}$	$\frac{.045}{[1,14]}$
202D274	$\frac{1.97}{[50,0]}$	$\frac{1.62}{[41,2]}$	$\frac{1.97}{[50,0]}$	$\frac{1.24}{[31,5]}$	$\frac{.56}{[14,2]}$	$\frac{8.00}{[203,2]}$	$\frac{6.21}{[157,7]}$	$\frac{.60}{[15,2]}$	$\frac{.12}{[3,0]}$	$\frac{.065}{[1,65]}$	$\frac{.82}{[20,8]}$	$\frac{.09}{[2,3]}$	$\frac{.055}{[1,40]}$
202D285	$\frac{2.47}{[62,7]}$	$\frac{1.85}{[47,0]}$	$\frac{2.47}{[62,7]}$	$\frac{1.54}{[39,1]}$	$\frac{.69}{[17,5]}$	$\frac{8.00}{[203,2]}$	$\frac{6.03}{[153,2]}$	$\frac{.63}{[16,0]}$	$\frac{.12}{[3,0]}$	$\frac{.08}{[2,0]}$	$\frac{.92}{[23,4]}$	$\frac{.10}{[2,5]}$	$\frac{.055}{[1,40]}$
202D296	$\frac{2.73}{[69,3]}$	$\frac{2.35}{[59,7]}$	$\frac{2.73}{[69,3]}$	$\frac{1.70}{[43,2]}$	$\frac{.77}{[19,6]}$	$\frac{8.00}{[203,2]}$	$\frac{5.64}{[143,3]}$	$\frac{.63}{[16,0]}$	$\frac{.12}{[3,0]}$	$\frac{.08}{[2,0]}$	$\frac{.93}{[23,6]}$	$\frac{.10}{[2,5]}$	$\frac{.055}{[1,40]}$
202D299	$\frac{3.22}{[81,8]}$	$\frac{2.64}{[67,1]}$	$\frac{3.22}{[81,8]}$	$\frac{2.01}{[51,1]}$	$\frac{.90}{[22,9]}$	$\frac{8.00}{[203,2]}$	$\frac{5.45}{[138,4]}$	$\frac{.63}{[16,0]}$	$\frac{.12}{[3,0]}$	$\frac{.08}{[2,0]}$	$\frac{1.23}{[31,2]}$	$\frac{.10}{[2,5]}$	$\frac{.055}{[1,40]}$



Revision : N1
Date : 29MAR11

Part Number : 202D211 thru 299
Description : Boot, Straight With Lip

Thermofit[®] Molded Parts
Specification Control Drawing


Part Number : 202D211 thru 299
Description : Boot, Straight With Lip

COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S-1017;S-1048;S-1030	Adhesive
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S-1017;S-1048;S-1030	Adhesive
-5	Neoprene	RT-501	/42	S-1017	
-6	Silicone	RT-602	N/A		
-8	Polyolefin, Space	RT-1308	N/A		
-12	*VITON, Flexible	RT-1312	N/A		
-25	Elastomer, Fluid Resistant	RT-1325	/42;/86	S-1017;S-1048	Adhesive
-130	Polyolefin, Flexible	RW-2008	/42;/86	S-1017;S-1048	Adhesive
-100	Polyolefin, Semi-flexible ZEROHAL™	RT-1323	/86;/184	S-1048;S-1030	Adhesive

*VITON is a Registered Trademark of Dupont

ORDERING INFORMATION



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



Revision : N1
Date : 29MAR11

Part Number : 202D211 thru 299
Description : Boot, Straight With Lip