

Very flexible highly flame retardant polyolefin tubing. UL and CSA recognised and marked. Low shrink temperature.

**Characteristics**

- Operating Temperature: -55°C to 125°C
- Minimum Shrink Temperature: 90°C
- Shrink Ratio: 2:1
- Dielectric Strength: 40kV/mm
- Standard Colour(s): Black, Red, Yellow, Green, Blue, White
- Specifications: UL224 125°C 600V VW-1, CSA C22.2 No. 198.1 125°C 600V OFT
- Marking: SUMITOMO-K CSA HS X PO TUBING 125° SUMITUBE F2 VW-1-F-



**Application Fields**

All general purpose applications in electronic and electromechanical industries. Light harnesses, bundling, colour coding, insulation of soldered or crimped connectors in electronic equipment.

**Remarks**

Other colours and 1.2m cut length available upon request.

Table of Standard Sizes and Packaging

Type/Size F2 (Inch)	Inside Diameter (mm)		Wall Thickness Recovered (nom.)	Quantity per Spool / Box (m)
	Expanded (min.)	Recovered (max.)		
3/64	1.20	0.60	0.33	300/900
1/16	1.60	0.80	0.36	300/900
3/32	2.40	1.20	0.44	150/900
1/8	3.20	1.60	0.44	150/900
3/16	4.80	2.40	0.44	60/600
1/4	6.4	3.20	0.56	60/300
3/8	9.5	4.80	0.56	60/300
1/2	12.7	6.4	0.56	60/300
3/4	19.1	9.5	0.69	60/180
1	25.4	12.7	0.77	60/180
1-1/2	38.1	19.1	0.87	60/180
2	50.8	25.4	0.97	60/120