


DOC NO	ISSUE	REVISION	PRODUCT REF.	DATE	QUALITY PLAN
QF/RD/05	01	00	FAR0201	24.09.14	
TECHNICAL SPECIFICATIONS				SIGNATURE	
				PRESIDENT (TECHNICAL)	

FULL BODY HARNESS (FAR0201)



DESIGN

- One dorsal attachment D-ring for fall arrest.
- Adjustable shoulder straps.
- Adjustable leg straps.
- Adjustable chest straps.
- Sit Strap.

WEBBING

- Material : Polyester
- Width : 44±1mm
- Breaking strength : 23 kN

STITCHING THREAD

- Material : High-tenacity polyester.

METAL COMPONENTS

- Material : High Strength steel.
- Plating : Galvanized with Yellow/Silver Passivation.
- Finish : Deburred & Shot Blasted.

VITAL TEST COMPLIANCE

- Static Strength : 15 kN or 1,530 kgf for 3 Minutes at each attachment element.
- Dynamic strength : Free fall from 4 meters height donned to a test dummy weighing 100 kg at each attachment element.


WEIGHT

- : 1075 gm ±10 gm



DOC NO	ISSUE	REVISION	PRODUCT REF.	DATE	QUALITY PLAN
QF/RD/05	01	00	FAR0208	10.10.14	
TECHNICAL SPECIFICATIONS				SIGNATURE	
				PRESIDENT (TECHNICAL)	

WORK POSITIONING LANYARD (FAR0208)



DESIGN

- Adjustable length upto 2 meters maximum.
- Adjustment by use of ring type adjuster.
- Karabiners [116F(C)] provide at both end for attachment.

WEBBING

- 33 MM Polyester Webbing.
- Breaking Strength greater than 30 kN.

METAL COMPONENTS

- Material : Forged alloy steel ring type adjuster.
- Plating : Zinc plated.
- Finish : Deburred & Polished.

VITAL TEST COMPLIANCE

- Static Strength : 15 kN for 3 Minutes.
- Dynamic strength : Free fall from 1 meter height with a test mass of 100 kg.

WEIGHT

- 2.0 Meter : 587 gm \pm 10 gm.