

8213 Coax - 75 Ohm Coax

 For more Information
 please call

1-800-Belden1

**General Description:**

14 AWG solid .064" bare copper conductor, gas-injected foam HDPE insulation, bare copper braid shield (95% coverage), polyethylene jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	14	Solid	BC - Bare Copper	.064

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.285

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

Overall Cable

Overall Nominal Diameter: 0.405 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-55°C To +80°C
Non-UL Temperature Rating:	80°C
Bulk Cable Weight:	78 lbs/1000 ft.
Max. Recommended Pulling Tension:	171 lbs.
Min. Bend Radius/Minor Axis:	4 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
RG Type:	11/U

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):

No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.1

Nominal Velocity of Propagation:

VP (%)

84

Nominal Delay:

Delay (ns/ft)

1.21

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.6

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.2
10	.4
50	.9
100	1.3
200	1.9
400	2.9
700	4.1
900	4.8
1000	5.2

Max. Operating Voltage - Non-UL:

Voltage

300 V RMS

Typical Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Typical SRL (dB)
		5	450	23

Notes (Overall)

Notes: 100% sweep tested. 5 MHz to 450 MHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8213	1 EA	0.000 LB			VB 1A-2-2-212/2 M
8213 0101000	1,000 FT	87.000 LB	BLACK	C	RG-11/U TYPE COAX
8213 0102000	2,000 FT	172.000 LB	BLACK	C	RG-11/U TYPE COAX
8213 010500	500 FT	44.000 LB	BLACK	C	RG-11/U TYPE COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-27-2012

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities

8213 Coax - 75 Ohm Coax

and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.