

SKINDICHT® SKZ-M

SKINDICHT® SKZ-M, metric brass cable gland with incised sealing ring and high mechanical stability, high strain relief



Optimum strain relief



Mechanical resistance

Benefits

With incised sealing ring for adjustment to several cable diameters
High strain relief
High mechanical stability

Application range

Saddle clamp strain relief gland for harsh application conditions.
Building sites
Plant engineering
Electric motor manufacturing

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Note

SKINDICHT® SHZ-M-XL is similar to the SKINDICHT® SHZ-M, but has an extended connection thread for thick walls
Counter nut to be used: SKINDICHT® SM-M

Example description:

SKZ-M 16/9

16 = connection thread

9 = PG function thread

SKINDICHT® SKZ-M**Technical Data**

Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Incised sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-30°C to +80°C

Note

Photographs are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SKZ-M**

Article number	Article designation / size	Ø F mm	Max. fitting size for installation (mm)	Function thread PG	SW1/SW2 mm	Total length C (mm)	Thread length, D (mm)
SKINDICHT® SKZ-M							
52106800	M 16 x 1,5	5 - 8	24	9	18 / 17	29	5
52106810	M 20 x 1,5	7 - 12	27	11	22 / 20	30	6
52106820	M 20 x 1,5	11 - 13	30	13.5	22 / 22	33.5	6
52106830	M 20 x 1,5	13 - 15	33	16	24 / 24	34.5	6
52106840	M 25 x 1,5	16 - 19.3	42	21	30 / 30	41	7
52106850	M 32 x 1,5	19 - 27	58	29	40 / 41	46	8
SKINDICHT® SKZ-M-XL							
52106805	M 16 x 1,5	5 - 8	24	9	18 / 17	34	10
52106815	M 20 x 1,5	7 - 12	27	11	22 / 20	34	10
52106825	M 20 x 1,5	11 - 13	30	13.5	22 / 22	37.5	10
52106835	M 20 x 1,5	13 - 15	33	16	24 / 24	38.5	10
52106845	M 25 x 1,5	16 - 19.3	42	21	30 / 30	45	11
52106855	M 32 x 1,5	19 - 27	58	29	40 / 41	51	13

Last Update (06.07.2017)

@2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16