




.187
(4.75)

△ CIRCUIT I.D.

MOUNTING EAR (2 PL)
(WHEN SPECIFIED)
SEE DETAIL 3 OR 4

.395
(10.03)

0.340
(8.64)

.145±.005
(3.68±0.13)

STANDARD
DETENT SHOWN.
OPTIONAL
POSITIVE LOCK
THIS SIDE ONLY
(SEE NOTE △5)


OPTIONAL POSITIVE LOCK
ONE SIDE ONLY
SCALE 4:1

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± .005	± .0007
3 PLACES ± .007	± .0010
2 PLACES ± .010	± .0015
1 PLACE ± .015	± .0020
ANGULAR ± 1 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	


.193
(4.90)

.812
(20.62)

0.233±.010
(5.92±0.25)



RECEPTACLE HOUSING
(1625-2R2 SHOWN)



RECEPTACLE HOUSING
(1625-2R3 SHOWN)

UPDATE TITLE BLOCK EC NO: UCP2007-1980 DRAWN BY: JJS CHKD: AELHAG APPR: FSM TH REV: AE1	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY JJS	DATE 1988/04/14	TITLE PLUG & RECEPTACLE 2 CIRCUIT HOUSINGS .062/(1.57) DIA.		
			4 PLACES ± ---	± ---	CHECKED BY RW	DATE 1988/04/14			
			3 PLACES ± ---	± .007	APPROVED BY RAS	DATE 1988/04/14	MOLEX INCORPORATED		
			2 PLACES ± 0.18	± 0.10	MATERIAL NO.				
			1 PLACE ± 0.25	± ---	SEE CHART		SD-1625-2*		
ANGULAR ± 1 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

