








LOC		DIST		REVISIONS				
CM	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
		W1		REVISED PER ECO-11-005027	16MAR2011	RK	HMR	



- PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- CONTACT IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN 0.00076 [0.000030] GOLD OVER CONTACT LENGTH INDICATED AND TIN LEAD ON SOLDER TAIL END.
- MATES WITH HOUSING 480706.
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- CONTACT IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN 0.00076 [0.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- DIMENSIONS IN BRACKETS ARE IN INCHES.



3 DIMENSIONAL MODEL
SCALE 4:1



SECTION B-B

SECTION A-A
SCALE 10:1

PHOSPOR BRONZE, GOLD 5	NYLON, UL94V-2,NATURAL	350432-4
PHOSPOR BRONZE, GOLD 2	NYLON, UL94V-2,NATURAL	350432-2
PHOSPOR BRONZE, PRE-TIN	NYLON, UL94V-2,NATURAL	350432-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL AND COLOR	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. WHITAKER 19JULY2005	NAME	
DIMENSIONS: mm[INCHES]		CHK S. RIDGILL 19JULY2005	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 19JULY2005	APPLICATION SPEC	
9 PLC ±			WEIGHT	
2 PLC ±			CUSTOMER DRAWING	
3 PLC ±0.13(.005)			SCALE 5:1	
5 PLC ±			SHEET 1 OF 1	
4 PLC ±			REV W1	
ANGLES ±0°30'				
FINISH SEE TABLE				