


> PE 22 A Bench drill

Characteristics :

- Digital display of the drilling depth
- Servo chuck-protective shield
- Drilling position laser device
- LED lighting
- The pulley cover is fitted with a safety claw-lock microswitch
- ON/OFF main switch fitted with an undervoltage coil
- Emergency stop with mechanical latching
- Transmission through timing belts and steel pulleys
- Spindle fitted with ball bearings
- Cast iron column
- Square table that can be tilted up to 45°, including a coolant collecting device
- Table powered through a rack
- Comes standard with a key less chuck, a chuck shank, a taper drift, a screw vice and a set of clamps

	Max drilling capacity (mm)	Morse taper	Column Ø (mm)	Spindle stroke (mm)	Quantity of speed	Spindle speed (tr/min)	Dimensions a x b x c (mm)	d (mm)	e (mm)	f (mm)	Table dimensions (mm)	Power (kW)			
PE 22 A	22	MT2	72	85	16	180 - 2770	660 x 980 x 430	160	630	440	286 x 286	0,55	230 V mono	49	20502055




..... PE 22 A

> Accessories

> Vices :

	For drilling machine	Type	Set of supports	Jaws width (mm)	Jaws height (mm)	Between axis (mm)	Max opening (mm)		
€ 100 A	PE 22 A	screw model	not include	100	25	135	110	2,8	20598002
€ 100 B	PE 22 A / PE 22 FE / PC 22 FC	fast tightening	not include	105	30	125	110	7	20598004
BSF 100 C	PE 22 A	screw model	include	100	34	125	90	4	20698024



> Set of support system* :

Set of supports	20598041
* 2 arbors M12 x 80 2 washers Ø 12 2 T slots M12 x 14 2 nuts M12 x 18	



> Taper drift :

For PE 22 A / PE 22 FE / PC 22 FC	20598039
1/2 manual	



> Key less chuck :

For PE 22 A / PE 22 FE / PC 22 FC / PC 30 FC / PC 30 FC TE / PC 40 FC / PC 40 FC TE	20598036
1 à 16 mm - B18	



> Chuck shank :

For PE 22 A / PE 22 FE / PC 22 FC	20598026
MT2 - B18	

