




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			U2	REVISED PER ECO-11-004587	11MAR11	RK	HMR




RECOMMENDED PC BOARD MOUNTING DIMENSIONS
RECOMMENDED STENCIL THICKNESS = 0.25 [.010]

- 1 0.000381 [.000015] GOLD IN THE CONTACT AREA,
0.00254-0.00508 [.000100-.000200] MATTE
TIN-LEAD ON THE SOLDER TAIL, ALL OVER
ALL OVER 0.00127 [.000050] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY FROM THE BASIC
DIMENSION LINE (NOT THE POST CENTERLINE)
TO THE SURFACE INDICED
- 4 ONE POLARIZATION SLOT FOR 2 AND 3 POSITION ASSEMBLIES ONLY.
- 5 SELECT POST TAILS FORMED TO PROVIDE CONNECTOR
HOLD DOWN UNTIL SOLDERED, CONFIGURATION
ACCEPTS 0.69-2.03 [.027-.080] THICK PRINTED
CIRCUIT BOARD (SEE DETAIL Z).
- 6 DIMENSIONS NOTED ARE FOR SOLDER
STENCIL LAYOUT FOR USE WITH
1.57±0.20 [.062±.008] THICK
PRINTED CIRCUIT BOARDS.
- 7 PARTS ARE PACKAGED IN GANG OF TUBES

- 8 OBSOLETE PART NO., REFER TO DWG 104909
FOR POS 13 THRU 25.
- 9 HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
COLOR-BLACK.
POSTS: BRASS.
- 10 0.000381 [.000015] GOLD IN THE CONTACT AREA,
0.00254-0.00508 [.000100-.000200] MATTE MATTE TIN ON
THE SOLDER TAIL, ALL OVER ALL OVER 0.00127 [.000050]
NICKEL.
- 11 SUPERSEDED

PART NO.	SUPERSEDED BY
1-104362-2	1-104909-2
1-104362-4	1-104909-4
1-104362-7	1-104909-7
2-104362-2	—
2-104362-3	—



SECTION X-X

10	33.02 [1.300]	30.99 [1.220]	27.94 [1.100]	11	12	6-104362-1
10	30.48 [1.200]	28.45 [1.120]	25.4 [1.000]	10	11	6-104362-0
10	27.94 [1.100]	25.91 [1.020]	22.86 [900]	9	10	5-104362-9
10	25.4 [1.000]	23.37 [920]	20.32 [800]	8	9	5-104362-8
10	22.86 [900]	20.83 [820]	17.78 [700]	7	8	5-104362-7
10	20.32 [800]	18.29 [720]	15.24 [600]	6	7	5-104362-6
10	17.78 [700]	15.75 [620]	12.7 [500]	5	6	5-104362-5
10	15.24 [600]	13.21 [520]	10.16 [400]	4	5	5-104362-4
10	12.7 [500]	10.67 [420]	7.62 [300]	3	4	5-104362-3
10	10.16 [400]	8.13 [320]	5.08 [200]	2	3	5-104362-2
10	7.62 [300]	5.59 [220]	2.54 [100]	1	2	5-104362-1
	66.04 [2.600]	64.01 [2.520]	60.96 [2.400]	24	25	2-104362-4
	63.5 [2.500]	61.47 [2.420]	58.42 [2.300]	23	24	2-104362-3
	60.96 [2.400]	58.93 [2.320]	55.88 [2.200]	22	23	2-104362-2
	58.42 [2.300]	56.39 [2.220]	53.34 [2.100]	21	22	2-104362-1
	55.88 [2.200]	53.85 [2.120]	50.8 [2.000]	20	21	2-104362-0
	53.34 [2.100]	51.31 [2.020]	48.26 [1.900]	19	20	1-104362-9
	50.8 [2.000]	48.77 [1.920]	45.72 [1.800]	18	19	1-104362-8
	48.26 [1.900]	46.23 [1.820]	43.18 [1.700]	17	18	1-104362-7
	45.72 [1.800]	43.69 [1.720]	40.64 [1.600]	16	17	1-104362-6
	43.18 [1.700]	41.15 [1.620]	38.1 [1.500]	15	16	1-104362-5
	40.64 [1.600]	38.61 [1.520]	35.56 [1.400]	14	15	1-104362-4
	38.1 [1.500]	36.07 [1.420]	33.02 [1.300]	13	14	1-104362-3
	35.56 [1.400]	33.53 [1.320]	30.48 [1.200]	12	13	1-104362-2
1	33.02 [1.300]	30.99 [1.220]	27.94 [1.100]	11	12	1-104362-1
1	30.48 [1.200]	28.45 [1.120]	25.4 [1.000]	10	11	1-104362-0
1	27.94 [1.100]	25.91 [1.020]	22.86 [900]	9	10	104362-9
1	25.4 [1.000]	23.37 [920]	20.32 [800]	8	9	104362-8
1	22.86 [900]	20.83 [820]	17.78 [700]	7	8	104362-7
1	20.32 [800]	18.29 [720]	15.24 [600]	6	7	104362-6
1	17.78 [700]	15.75 [620]	12.7 [500]	5	6	104362-5
1	15.24 [600]	13.21 [520]	10.16 [400]	4	5	104362-4
1	12.7 [500]	10.67 [420]	7.62 [300]	3	4	104362-3
1	10.16 [400]	8.13 [320]	5.08 [200]	2	3	104362-2
1	7.62 [300]	5.59 [220]	2.54 [100]	1	2	104362-1

PLATING	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
---------	---	---	---	---	------------------	----------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G DOUTY 2--22--88		 TE Connectivity	
		CHK T C CLARK 2--22--88			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSY, AMPMODU MTE, VERTICAL SINGLE ROW, .100 C/L, .025 SQ POST POLARIZED, WITH LATCHING & HOLD DOWN	
		APVD —			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± —		PRODUCT SPEC —			
ANGLES ± — ± —		APPLICATION SPEC —			
MATERIAL 		FINISH SEE TABLE		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-104362	
				RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 of 1	
				REV 1/2	